



TECHNICAL INFORMATION

Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Body Type:	Aluminium
Dimmable:	No
Rated Load:	Max 60W
Dimension:	250x1110mm

POLE LAMPS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 7530 - 938

[View more details](#)

**CLASSICAL
DESIGN**

**ALUMINIUM AND
PC BODY**



**3 YEAR
WARRANTY**



**IP44
RATING**

FEATURES

- Traditional garden lamps designed to meet modern day requirements
- Strong and sturdy Aluminium body
- Offering IP44 Ingress protection
- Compatible with E27 holder type (Fitting only - light not included)
- Suitable for gardens, patio, pathways etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs):	2.99
Unit CBM:	0.057915
Dimension:	250x1110mm

MASTER BOX PACKAGING

Box Qty:	1
Qty Per Pallet:	24
Length (Box) mm:	270
Width (Box) mm:	330
Height (Box) mm:	650

LISTING DETAILS

Commodity Code:	9405109890
EanCode:	3800157630061