



## TECHNICAL INFORMATION

Wireless Frequency:	2.412-2.484 Ghz
Input Power:	AC:90-250V, 50/60Hz
Input Current:	10A
Long Life:	10,000 Times
Body Type:	PC
Dimension:	67x67x102mm
Rated Load:	Max 20W
On/Off Cycles:	>10000



## FEATURES

- Wi-Fi enabled E27 lamp holder
- Sturdy PC build
- Wireless frequency: 2.4GHz
- Easy to install and pair with the app
- Compatible with Amazon Alexa and Google Home
- Can be controlled via V-TAC Smart Home app or Alexa and Google Home

## LAMP HOLDER

WiFi-supported home solutions to convert any device into a smart device, and ultimately convert any home into a smart home. Have a systematic, unified control on all your smart devices through the official V-TAC app, Amazon Alexa, and Google Home.

*One brand, endless solutions..testing*

SKU: 8421 -

[View more details](#)

**Wifi Lamp Holder**  
3 Step Processing

**Step.1**  
**Plug the device &**  
Register an account with QR Code

**Step.2**  
**Pair the device with**  
V-TAC Smart Home app

**Step.3**  
Link the device to  
Amazon Alexa or Google Home

## PACKAGING

Gross Weight (Kgs):	0.085
Unit CBM:	0.00049
Dimension:	67x67x102mm

## MASTER BOX PACKAGING

Box Qty:	50
Qty Per Pallet:	2000
Length (Box) mm:	70
Width (Box) mm:	70
Height (Box) mm:	100

## LISTING DETAILS

EanCode: 3800157637343