



Specifications

Contact form	: 2 form C.
Dielectric Strength Between Coil and Contact	: 4kV
Creepage distance	: 8mm.
Dimension	: 29mm × 12.6mm × 20.8mm
Slim type with low height.	


Specification Table

Contact Data		
Contact Material		Ag Alloy
Contact Rating		Resistive: 5A 250V AC / 24V DC TV Rating : TV-5 Inductive: 5A 250V AC / 24V DC (COSØ = 0.4, L/R = 7ms)
Contact Resistance		Max. 100mΩ (6V DC 1A)
Load	Max. Switching Voltage	250V AC / 30V DC
	Max. Switching Current	5A
	Max. Switching Power	1,250VA, 120W
	Min. Switching Load	5V dc, 100mA
Life	Electrical	100,000 Operations
		20,000 Operations (COSØ = 0.4 L/R = 7ms)
	Mechanical	10,000,000 Operations
Coil Data		
Nominal Coil Power		540mW, 720mW
General Data		
Insulation Resistance		Min. 1,000MΩ 500V DC
Dielectric Strength	Between Open Contacts	1,000V AC, 1 Min
	Between Coil and Contacts	4,000V AC, 1 Min
Operate Time		Maximum 15ms
Release Time		Maximum 8ms
Operating Temperature		-30°C to +55°C (720mW)
		-30°C to +70°C (540mW)
Humidity		35 to 95% RH, +40°C
Shock Resistance	Endurance	1,000m/s ²
	Misoperation	100m/s ²
Vibration Resistance	Endurance	10 to 55Hz, 1.5mm Double Amplitude
	Misoperation	

Coil Data


Nominal Voltage V DC	Coil Resistance $\Omega \pm 10\%$	Operate Voltage $\leq V$ DC	Release Voltage $\geq V$ DC	Coil Power mW	Part Number
5	35	3.75	0.5	720	HRM1-S-DC5V C
9	112.5	6.75	0.9		HRM1-S-DC9V C
12	200	9	1.2		HRM1-S-DC12V C
24	800	18	2.4		HRM1-S-DC24V C

Out Line, Wiring Diagram, Mounting Hole Layout




Characteristic Chart Data


Timing (Standard)




Coil Temperature Rise




Operate Range




Maximum Switching Power



Life Curves



Part Number Explanation



- Coil Sensitivity : Blank - Standard (720mW).
- Enclosure : S-Plastic sealed type.
- Coil Voltage : DC5V, DC9V, DC12V and DC24V.
- Contact Form : C-2 Form C.

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.