

**SAK Series**  
**Q 3 SAK6N****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image**

Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	Q 3 SAK6N
Order No.	<a href="#">0456800000</a>
Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 3
GTIN (EAN)	4008 1901 10277
Qty.	50 pc(s).

Creation date October 21, 2020 9:51:50 AM CEST

Catalogue status 09.10.2020 / We reserve the right to make technical changes.

## SAK Series Q 3 SAK6N

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	21.8 mm	Width (inches)	0.858 inch
Height	6 mm	Height (inches)	0.236 inch
Depth	20.5 mm	Depth (inches)	0.807 inch
Net weight	7.16 g		

### Temperatures

Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Storage temperature	-25 °C...55 °C		

### Material data

Material	CuSn	Colour	grey
----------	------	--------	------

### System specifications

Version	for cross-connection link
---------	---------------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

### Dimensions

Pitch in mm (P)	6 mm
-----------------	------

### Rating data

Rated current	41 A
---------------	------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40	UNSPSC	30-21-18-01

### Approvals

Approvals



ROHS Conform

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>