



FEATURES

- Basic/supplementary isolation to UL60950²
- ANSI/AAMI ES60601-1
- Single and dual outputs
- UL 94V-0 package material
- SIP package style
- 5.2kVDC isolation 'Hi Pot Test'
- 3.3V, 5V, 12V, 15V & 24V inputs
- 3.3V, 5V, 9V, 12V & 15V output
- Internal SMD construction
- Fully encapsulated with toroidal magnetics
- Pin compatible with the MEV, NMV, NMK, MEJ2, & NMJ series
- Characterised CMTI >200kV/μS
- Continuous barrier withstand voltage 2.4kVDC

PRODUCT OVERVIEW

The MEJ1 series are single and dual output DC-DC converters in a 7 pin SIP package style offering an isolation and insulation upgrade path from the NMV & MEV1 series¹. The MEJ1 series has UL60950 and ANSI/AAMI ES60601-1 recognition, which makes it ideal for applications where safety and miniaturisation are of paramount importance.

SELECTION GUIDE

Order Code	Nominal Input Voltage	Output Voltage	Output Current	Input Current (Typ)	Load Regulation (Typ)	Load Regulation (Max)	Ripple & Noise (Typ) ³	Ripple & Noise (Max) ³	Efficiency (Min)	Efficiency (Typ)	MTTF ¹
	V	V	mA	%	mVp-p	%	kHrs				
MEJ1S0303SC	3.3	3.3	303	410	8.5	11	42	55	67	70	3653
MEJ1S0305SC	3.3	5	200	400	9	10	33	45	68	71.5	3810
MEJ1S0503SC	5	3.3	303	280	6.5	8	20	40	66	69	4117
MEJ1S0505SC	5	5	200	270	5.5	7	24	40	68	72	4082
MEJ1S0509SC	5	9	111	265	4.5	5	20	40	70	74	3939
MEJ1S0512SC	5	12	83	260	4.5	7	22	40	71	74	3816
MEJ1S0515SC	5	15	66	260	5	6	22	40	72	75	3412
MEJ1S1203SC	12	3.3	303	110	6	7	25	45	69	72	3461
MEJ1S1205SC	12	5	200	110	5	6	21	40	71	74.5	3319
MEJ1S1209SC	12	9	111	105	4	5	18	40	73	76.5	3218
MEJ1S1212SC	12	12	83	105	3.5	5	19	40	73	76.5	3494
MEJ1S1215SC	12	15	66	105	4	5	16	40	73	77	3150
MEJ1S1505SC	15	5	200	90	5	6	23	45	70	74	3048
MEJ1S1509SC	15	9	111	85	4	5	18	40	72	76	2963
MEJ1S1512SC	15	12	83	85	4	5	20	40	72	76.5	2733
MEJ1S1515SC	15	15	66	85	4	5	19	35	73	76.5	2333
MEJ1S2405SC	24	5	200	55	5	6	23	40	71	75	3353
MEJ1S2409SC	24	9	111	55	4	7	17	40	72	77	2940
MEJ1S2412SC	24	12	83	55	4	5	19	40	72	78	2987
MEJ1S2415SC	24	15	66	55	3.5	5	17	40	74	78	2517
MEJ1D0503SC	5	±3.3	±151	280	6	8	19	40	67	70	4511
MEJ1D0505SC	5	±5	±100	275	5	6	23	35	69	72	4012
MEJ1D0509SC	5	±9	±55	265	4	6	16	35	69	74	3492
MEJ1D0512SC	5	±12	±42	260	4	5	15	30	72	74.5	3485
MEJ1D0515SC	5	±15	±33	260	4	5	13	35	71	75.5	2844
MEJ1D1203SC	12	±3.3	±151	110	5.5	6	19	40	70	73	3461
MEJ1D1205SC	12	±5	±100	110	4.5	5	18	40	72	75.5	3317
MEJ1D1209SC	12	±9	±55	110	4	5	15	35	73	77	2908
MEJ1D1212SC	12	±12	±42	110	3.5	5	14	30	74	76.5	2911
MEJ1D1215SC	12	±15	±33	110	4	5	11	35	73	77	2713
MEJ1D1505SC	15	±5	±100	90	4.5	5	19	40	72	75	3274
MEJ1D1509SC	15	±9	±55	85	4	5	14	35	73	76.5	3229
MEJ1D1512SC	15	±12	±42	85	3.5	5	13	35	73	77	2872
MEJ1D1515SC	15	±15	±33	85	3.5	5	20	35	73	76.5	2440
MEJ1D2405SC	24	±5	±100	55	4.5	5	19	40	72	76.5	3316
MEJ1D2409SC	24	±9	±55	55	3.5	5	17	35	73	78	3208
MEJ1D2412SC	24	±12	±42	55	3.5	5	12	35	74	78	3362
MEJ1D2415SC	24	±15	±33	55	3.5	5	14	35	74	78.5	2697

INPUT CHARACTERISTICS

Parameter	Conditions	Min.	Typ.	Max.	Units
Voltage range	Continuous operation, 3V input types	2.97	3.3	3.63	V
	Continuous operation, 5V input types	4.5	5	5.5	
	Continuous operation, 12V input types	10.8	12	13.2	
	Continuous operation, 15V input types	13.5	15	16.5	
	Continuous operation, 24V input types	21.6	24	26.4	
Input reflected ripple	3.3V input types		40		mA
	5V input types		24		
	12V & 15V input types		12		
	24V input types		8		

1. Calculated using MIL-HDBK-217 FN2 calculation model with nominal input voltage at full load.

2. See safety approvals section for limitations of use.

3. See ripple & noise test method.

All specifications typical at T_A=25°C, nominal input voltage and rated output current unless otherwise specified.

ISOLATION CHARACTERISTICS

Parameter	Conditions	Min.	Typ.	Max.	Units
Isolation test voltage	Production tested for 1 second	5200			VDC
	Qualification tested for 1 second	7000			
	Qualification tested for 1 minute	5200			
Resistance	Viso= 500VDC		1		GΩ
Isolation capacitance			3		pF
Continuous barrier withstand voltage	Non-safety barrier application			2400	V
UL60950-1	Basic/supplementary			200	Vrms
ANSI/AAMI ES60601-1	1 MOOP			200	

OUTPUT CHARACTERISTICS

Parameter	Conditions	Min.	Typ.	Max.	Units
Rated Power ²	T _A =-40°C to 85°C			1	W
Voltage Set Point Accuracy	See tolerance envelopes				
Line regulation	High V _{IN} to low V _{IN}		1.1	1.2	%/%

TEMPERATURE CHARACTERISTICS

Parameter	Conditions	Min.	Typ.	Max.	Units
Specification	All output types (see safety approval section for limitations)	-40		85	°C
Storage		-55		125	
	MEJ1S1212SC, MEJ1S1512SC, MEJ1S2412SC, MEJ1D1215SC, MEJ1D1512SC, MEJ1D2412SC, MEJ1D2415SC, MEJ1S1215SC, MEJ1S1509SC, MEJ1S2409SC			13	
	MEJ1D1205SC, MEJ1D1209SC, MEJ1D2405SC, MEJ1D2409SC, MEJ1S1209SC, MEJ1S1515SC, MEJ1S2415SC, MEJ1D1212SC, MEJ1D1509SC, MEJ1S0515SC, MEJ1S2405SC, MEJ1D0512SC, MEJ1D0515SC, MEJ1D1515SC, MEJ1S1505SC, MEJ1D0505SC, MEJ1D0509SC, MEJ1D1203SC, MEJ1D1505SC, MEJ1S0509SC, MEJ1S0512SC, MEJ1S1205SC			17	
	MEJ1S0505SC, MEJ1S1203SC, MEJ1D0503SC, MEJ1S0303SC, MEJ1S0305SC, MEJ1S0503SC			21	
Cooling	Free air convection				

GENERAL CHARACTERISTICS

Parameter	Conditions	Min.	Typ.	Max.	Units
Switching frequency	All types		50		kHz

ABSOLUTE MAXIMUM RATINGS

Short-circuit protection	48 Hours
Lead temperature 1mm from case for 10 seconds	260°C
Wave Solder	Wave Solder profile not to exceed the profile recommended in IEC 61760-1 Section 6.1.3. Please refer to application notes for further information.
Input voltage V _{IN} , MEJ1x03xxSC	5V
Input voltage V _{IN} , MEJ1x05xxSC	7V
Input voltage V _{IN} , MEJ1x12xxSC	15V
Input voltage V _{IN} , MEJ1x15xxSC	18V
Input voltage V _{IN} , MEJ1x24xxSC	28V

TECHNICAL NOTES**ISOLATION VOLTAGE**

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions MEJ1 series of DC-DC converters are all 100% production tested at 5.2kVDC for 1 second and qualification tested at 7kVDC for 1 second, 5.2kVDC for 1 minute.

The MEJ1 series is recognised by Underwriters Laboratory, please see safety approval section for more information. When the insulation in the MEJ1 series is not used as a safety barrier, i.e. provides functional isolation only, continuous or switched voltages across the barrier up to 2.4kV are sustainable. This is established by measuring the partial discharge Inception voltage in accordance with IEC 60270. Please contact Murata for further information.

REPEATED HIGH-VOLTAGE ISOLATION TESTING

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.

SAFETY APPROVAL**ANSI/AAMI ES60601-1**

The MEJ1 series have recognised by Underwriters Laboratory (UL) to ANSI/AAMI ES60601-1 and provides 1 MOOP (Means Of Operator Protection) based upon a working voltage of 200 Vrms max and 280 Vpk max., between Primary and Secondary and between Primary and its Enclosure, in a maximum ambient temperature of 85°C and/or case temperature limit of 130°C (case temperature measured on the face opposite the pins).

File Number E202895 applies.

UL60950

The MEJ1 series have been recognised by Underwriters Laboratory (UL) to UL60950 for basic/supplementary insulation to a working voltage of 200Vrms in a maximum ambient temperature of 85°C and/or case temperature limit of 130°C (case temperature measured on the face opposite the pins).

File number E151252 applies.

Creepage and clearance 2mm

Working altitude 4000m

FUSING

The MEJ1 Series of converters are not internally fused so to meet the requirements of UL an anti-surge input line fuse should always be used with ratings as defined below.

MEJ1x03xxSC 1A

MEJ1x05xxSC 1A

MEJ1x12xxSC 500mA

MEJ1x15xxSC 500mA

MEJ1x24xxSC 200mA

All fuses should be UL recognized and rated to at least the maximum allowable DC input voltage.


RoHS COMPLIANCE INFORMATION

This series is compatible with RoHS soldering systems with a peak wave solder temperature of 260°C for 10 seconds. Please refer to [application notes](#) for further information. The pin termination finish on this product series is Tin Plate, Hot Dipped over Matte Tin with Nickel Preplate. The series is backward compatible with Sn/Pb soldering systems. For further information, please visit www.murata-ps.com/rohs

ENVIRONMENTAL VALIDATION TESTING

The following tests have been conducted on this product series, please contact Murata if further information about the tests is required.

Test	Standard	Condition
Temperature cycling	MIL-STD 883 1010, Condition B	10 cycles between two chambers set to achieve -55°C and +125°C. The dwell time shall not be less than 10min.
Humidity bias	JEDEC STD 22-A101	85°C ± 2°C, 85% ± 5% R.H. for >1000 hours.
Storage life	JEDEC JESD22-A103, Condition A	125°C +10/-0°C for ≥1000 hours.
Vibration	MIL STD 883 Method 2007, Condition A	1.5mm pk-pk / 20g pk min, 20-2000Hz, 4 sweeps in each of 3 mutually perpendicular axes at 3 oct/min.
Shock	MIL STD 883 method 2002, Condition A	500g 1.0ms half sine, 5 shocks in each direction of 3 mutually perpendicular axes.
ESD	JESD22-A114	HBM Testing Standard at 3 stress levels: 2.0kV, 4.0kV and 8.0kV.
Bump	IEC Class 4M5 offETS 300 019-2-4	Shock Spectrum Type II, 6mS duration, 250m/s ² 500 bumps in 6 directions.
Solderability	IPC/ECA J-STD-002, Test A1	For lead free solderability the parts are conditioned in a steam ager for 8 hours ± 15 min. at a temperature of 93±3°C. Dipped in solder at 255°C ±5°C for 5 +0/-0.5 seconds. For leaded solderability the parts are conditioned in a steam ager for 8 hours ± 15 min. at a temperature of 93±3°C. Dipped in solder at 245°C ±5°C for 5 +0/-0.5 seconds
Solder heat	JEDEC JESD22-B106	The test sample is subjected to a molten solder bath at 260 ±5°C for 10 seconds (96SC tin/silver/copper).
Solder heat (hand)	MIL-STD 202 Method 210, Condition A	The soldering iron is heated to 350°C ± 10°C and applied to the terminations for a duration of 4 to 5 seconds.
Solvent cleaning	Resistance to cleaning agents.	Solvent – Novec 71IPA & Topkleen EL-20A. Pulsed ultrasonic immersion 45°C- 65°C
Solvent Resistance	MIL-STD 883 Method 2015	Separate samples subjected to solvent A, solvent B and solvent D
Lead Integrity (Adhesion)	MIL-STD 883 Method 2025	Leads are bent through 90° until a fracture occurs.
Lead Integrity (Fatigue)	MIL-STD 883 Method 2004, condition B ₂	The leads are bent to an angle of 15°. Each lead is subjected to 3 cycles.
Lead Integrity (Tension/Pull)	MIL-STD 883 Method 2004, Condition A ₁	Pull of 0.227kg applied for 30 seconds. The force is then increased until the pins snap.

PART NUMBER STRUCTURE

APPLICATION NOTES

Minimum load

The minimum load to meet datasheet specification is 10% of the full rated load across the specified input voltage range. Lower than 10% minimum loading will result in an increase in output voltage, which may rise to typically double the specified output voltage if the output load falls to less than 5%.

Gate Drive Applications Advisory Note


For general guidance for product usage in gate drive applications please refer to ["gate drive application notes"](#).

Capacitive loading and start up

Typical start up times for this series, with a typical input voltage rise time of 2.2 μ s and output capacitance of 10 μ F, are shown in the table below. The product series will start into a capacitance of 47 μ F with an increased start time, however, the maximum recommended output capacitance is 10 μ F.

Typical Start-Up Wave Form

	Start-up time μs		Start-up time μs		Start-up time μs
MEJ1S0303SC	900	MEJ1S1509SC	2400	MEJ1D1205SC	1200
MEJ1S0305SC	2000	MEJ1S1512SC	2700	MEJ1D1209SC	3600
MEJ1S0503SC	500	MEJ1S1515SC	3800	MEJ1D1212SC	3900
MEJ1S0505SC	2000	MEJ1S2405SC	1700	MEJ1D1215SC	6000
MEJ1S0509SC	3200	MEJ1S2409SC	2300	MEJ1D1505SC	1200
MEJ1S0512SC	7500	MEJ1S2412SC	2200	MEJ1D1509SC	3200
MEJ1S0515SC	10500	MEJ1S2415SC	3600	MEJ1D1512SC	3300
MEJ1S1203SC	600	MEJ1D0503SC	700	MEJ1D1515SC	4800
MEJ1S1205SC	1200	MEJ1D0505SC	1600	MEJ1D2405SC	1100
MEJ1S1209SC	2900	MEJ1D0509SC	3700	MEJ1D2409SC	2000
MEJ1S1212SC	2900	MEJ1D0512SC	4200	MEJ1D2412SC	3300
MEJ1S1215SC	3900	MEJ1D0515SC	7000	MEJ1D2415SC	6400
MEJ1S1505SC	1100	MEJ1D1203SC	600		




Ripple & Noise Characterisation Method

Ripple and noise measurements are performed with the following test configuration.

C1	1 μ F X7R multilayer ceramic capacitor, voltage rating to be a minimum of 3 times the output voltage of the DC-DC converter
C2	10 μ F tantalum capacitor, voltage rating to be a minimum of 1.5 times the output voltage of the DC-DC converter with an ESR of less than 100m Ω at 100 kHz
C3	100nF multilayer ceramic capacitor, general purpose
R1	450 Ω resistor, carbon film, $\pm 1\%$ tolerance
R2	50 Ω BNC termination
T1	3T of the coax cable through a ferrite toroid
RLOAD	Resistive load to the maximum power rating of the DC-DC converter. Connections should be made via twisted wires
	Measured values are multiplied by 10 to obtain the specified values.


Differential Mode Noise Test Schematic




TOLERANCE ENVELOPES

The voltage tolerance envelope shows typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading.


DUAL 1203,1515, 2412, SINGLE 0303, 0305, 1203




DUAL 1209, 1509, 2409




DUAL 0515, SINGLE 1515, 2415




DUAL 1512, SINGLE 1212, 1512, 2412



DUAL 0512, SINGLE 1209, 1509




DUAL 1212, 1215, 2415, SINGLE 0509, 0512, 1215, 2409




TOLERANCE ENVELOPES


SINGLE 1205, 1505, 2405, 0515




DUAL 1205, 0505, 1505, 2405








DUAL 0509, 0503, SINGLE 0503, 0505







TEMPERATURE DERATING GRAPH



EFFICIENCY VS LOAD Single Output




EFFICIENCY VS LOAD Dual Output



PACKAGE SPECIFICATIONS

MECHANICAL DIMENSIONS




All dimensions in mm ± 0.25 mm (inches ± 0.01). All pins on a 2.54 (0.1) pitch and within ± 0.25 (0.01) of true position.

* Pin not fitted on single output variants.

Weight: 4.3g


TUBE OUTLINE DIMENSIONS



Unless otherwise stated all dimensions in mm ± 0.5 mm (inches ± 0.02).

Tube Quantity: 25

RECOMMENDED FOOTPRINT DETAILS



* Hole not required for single output variants.
All dimensions in mm ± 0.25 mm (inches ± 0.01).



This product is subject to the following [operating requirements](#) and the [Life and Safety Critical Application Sales Policy](#). Refer to: <http://www.murata-ps.com/requirements/>

Murata Power Solutions (Milton Keynes) Ltd. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.