

Electra House, 32 Southtown Road Great Yarmouth, Norfolk NR31 0DU, England Telephone +44 (0)1493 602602 Fax +44 (0)1493 665111 Email:sales@midasdisplays.com www.midasdisplays.com

MD128128A6W-FPTLW 128 x		LCD Module		
		Specification		
Version: 1		Date: 29/07/2020		
	Revision			
1	27/07/2020	First Issue		

Disp <b>l</b> ay F					
Resolution	128 x 128				
Appearance	Black on White				
Logic Voltage	3V				
Interface	Multi				
Font Set	N/A	CC	mpliant		
Display Mode	Transflec <mark>tiv</mark> e		mphant		
LC Type	FSTN				
Module Size	60.00 x 62.79 x 8.60 mm				
Operating Temperature	<b>-</b> 20°C ∼ +70°C				
Construction	<ul><li>Manula cob</li></ul>	Box Quantity	Weight / Display		
LED Backlight	White	***			

Disp	Display Accessories				
Part Number	Description				

Optional Variants			
Appearances	Voltage		

#### **General Specification**

The Features is described as follow:

■ Number of dots: 128 x 128

■ Module dimension: 60.0 x 62.79 x 8.6 mm

■ View area: 42.0 x 42.0 mm

Active area: 44.0 x 44.0 mm

■ Dot size: 0.308 x 0.308 mm

■ Dot pitch: 0.310 x 0.310 mm

■ LCD type: FSTN Positive Transflective

■ Duty: 1/136 Duty,1/12 Bias


■ View direction: 6 o'clock

■ Backlight Type: LED White

### **Interface Pin Function**

Pin No.	SYMBOL	Function			
1	VDD	Power supply			
2	NC	lo Connection			
3	VSS	Ground			
4	CSB	Chip select input pin.			
5	A0	It determines whether the access is related to data or command.			
6	ERD	Read / Write execution control pin.			
7	RWR	Read / Write execution control pin.			
8	RSTB	Hardware reset input pin			
9-16	D0-D7	When using 8-bit parallel interface: 8080 or 6800 mode:8 bit bi-directional data bus When using serial interface: 4-line SPI or 3-line SPI mode  D[7:4]: fix to "H" by VDD1. D[3:1]: serial input/output data (SDA).  D[0]: serial input clock (SCL). D1 to D3 must be connected together (SDA)  When using serial interface: I2C interface  D[7]: SA[1], I2C slave address bit. Must be connected to VDD1 or VSS1. D[6]: SA[0], I2C slave address bit. Must be connected to VDD1 or VSS1.  D[5:4]: fix to "H" by VDD1. D[3:2]: SDA_OUT, serial data and acknowledge output for the I2C interface. D[1]: SDA_IN, serial input data D[0]: SCL, serial input clock.  D1 to D3 must be connected together (SDA)  CSB must be fixed to "L" by VSS1.			
17	Α	Anode input for LED backlight.			
18	K	Cathode input for LED backlight			

## **Contour Drawing**




### **Optical Characteristics**

Item	Symbol	Condition	Min	Тур	Max	Unit
	θ	CR≧2	25	30	1	ψ= 180°
Viou Anglo	θ	CR≧2	35	40	1	ψ= 0°
View Ang <b>l</b> e	θ	CR≧2	35	40	_	ψ= 90°
	θ	CR≧2	25	30		ψ= 270°
Contrast Ratio	CR	_	3	4	_	_
Pagnanga Tima	T rise	_	_	150	225	ms
Response Time	T fa <b>ll</b>	_	_	220	330	ms




#### Definition of Response Time (Tr, Tf)



#### **Conditions:**

Frame Frequency: 64 HZ Driving Waveform: 1/N duty, 1/a bias

#### Definition of viewing angle(CR≥2)



### **Absolute Maximum Ratings**

Item	Symbol	Min	Тур	Max	Unit
Operating Temperature	Тор	<del>-</del> 20	_	+70	$^{\circ}$
Storage Temperature	T <sub>ST</sub>	-30	_	+80	${\mathbb C}$
Power Supply Voltage	VDD	-0.3		4.0	V
LCD Power supply voltage	VLCD	-0.3		20	٧
LCD Power supply voltage	V0-XV0	-0.3	ı	19	٧
Input voltage	VIN	-0.3		VDD+0.3	٧

### **Electrical Characteristics**

ltem	Symb <mark>ol</mark>	Condition	Min.	Тур.	Max.	Unit
Supply Voltage For Logic	V <sub>DD</sub> -V <sub>SS</sub>	-	2.7	3.0	3.3	V
		Ta=-20℃	_	_	-	V
Supply Voltage For LCD	Vop	Ta=25℃	13.7	14.0	14.3	V
9		Ta=70℃	_	_	_	V
Input High Volt.	VIH	_	0.7 V <sub>DD</sub>	_	V <sub>DD</sub>	V
Input Low Volt.	VIL		Vss		0.3 V <sub>DD</sub>	V
Output High Volt.	Vон	1	0.8 V <sub>DD</sub>	ı	V <sub>DD</sub>	V
Output Low Volt.	Vol		Vss		0.2 V <sub>DD</sub>	V
Supply Current	l <sub>DD</sub>	V <sub>DD</sub> =3.0V	_	2.0	_	mA

Please kindly consider to design the Vop to be adjustable while programing the software to match LCD contrast tolerance.


### **Backlight Information**

#### **Specification**

Parameter	Symbol	Min	Тур	Max	Unit	Test Condition
Supply Current	ILED	36	48	60	mA	V=3.5V
Supply Voltage	V	_	3.5	_	V	_
Reverse Voltage	VR	_	_	5	V	_
Chromaticity	Х	0.25	0.27	0.30	_	_
Coordinates	Υ	0.25	0.27	0.30	_	_
Luminance (Without LCD)	IV	800	1000	_	cd/m²	V=3.5V
LED Life Time (For Reference only)	_	A	50K		Hr.	ILED=48mA 25℃,50-60%RH, (Note 1)
Color	White				1/	

Note: The LED of B/L is drive by current only, drive voltage is for reference only. drive voltage can make driving current under safety area (current between minimum and maximum).

Note 1:50K hours is only an estimate for reference.



### Reliability

Content of Reliability Test (Wide temperature, -20℃~70℃)

	Environmental Test					
Test Item	Content of Test	Test Condition	Not e			
High Temperature storage	Endurance test applying the high storage temperature for a long time.	80℃ 96hrs	2			
Low Temperature storage	Endurance test applying the low storage temperature for a long time.	-30℃ 96hrs	1,2			
High Temperature Operation	Endurance test applying the electric stress (Voltage & Current) and the thermal stress to the element for a long time.	70℃ 96hrs				
Low Temperature Operation	Endurance test applying the electric stress under low temperature for a long time.	-20℃ 96hrs	1			
High Temperature/ Humidity storage	The module should be allowed to stand at 40 °C,90%RH max For 96hrs under no-load condition excluding the polarizer, Then taking it out and drying it at normal temperature.	40℃,90%RH 96hrs	1,2			
Therma <b>l</b> shock resistance	The sample should be allowed stand the following 10 cycles of operation  -20°C 25°C 70°C  30min 5min 30min 1 cycle	- <mark>20</mark> ℃/70℃ 10 cycles				
Vibration test	Endurance test applying the vibration during transportation and using.	Total fixed amplitude: 1.5mm Vibration Frequency: 10~55Hz One cycle 60 seconds to 3 directions of X,Y,Z for Each 15 minutes	3			
Static electricity test	Endurance test applying the electric stress to the terminal.	VS=±600V(contact)	_			

Note1: No dew condensation to be observed.

Note2: The function test shall be conducted after 4 hours storage at the normal Temperature and humidity after remove from the test chamber.

Note3: The packing have to including into the vibration testing.

# Inspection specification

NO	Item	Criterion	AQL
01	Electrical Testing	<ol> <li>1.1 Missing vertical, horizontal segment, segment contrast defect.</li> <li>1.2 Missing character, dot or icon.</li> <li>1.3 Display malfunction.</li> <li>1.4 No function or no display.</li> <li>1.5 Current consumption exceeds product specifications.</li> <li>1.6 LCD viewing angle defect.</li> <li>1.7 Mixed product types.</li> <li>1.8 Contrast defect.</li> </ol>	0.65
02	Black or white spots on LCD (display only)	<ul> <li>2.1 White and black spots on display ≤0.25mm, no more than three white or black spots present.</li> <li>2.2 Densely spaced: No more than two spots or lines within 3m</li> </ul>	2.5
. 03	LCD black spots, white	3.1 Round type : As following drawing $\Phi = (x + y) / 2$	
	spots, contamination (non-display)	3.2 Line type : (As following drawing)  Length Width Acceptable Q TY  W $\leq$ 0.02 Accept no dense L $\leq$ 3.0 0.02 < W $\leq$ 0.03 L $\leq$ 2.5 0.03 < W $\leq$ 0.05 As round type	<del> </del>
04	Polarizer bubbles	If bubbles are visible, judge using black spot specifications, not easy to find, must check in specify direction. $ \begin{array}{c ccccccccccccccccccccccccccccccccccc$	

NO	Item		Criterion		AQL	
05	Scratches	Follow NO.3 LCD black	Follow NO.3 LCD black spots, white spots, contamination			
		Symbols Define: x: Chip length y: 0	y: Chip width  Not over viewing area  Not exceed 1/3k	thickness D side length  n panels:  x: Chip length  x≤1/8a  x≤1/8a	2.5	
		1/2t < z ≤ 2t	Not exceed 1/3k	x≦1/8a		
			chips, x is the total leng	gth of each chip.		

NO	Item	Criterion						
	G <b>l</b> ass crack	Symbols:  x: Chip length y: Chip width z: Chip thickness k: Seal width t: Glass thickness a: LCD side length L: Electrode pad length 6.2 Protrusion over terminal: 6.2.1 Chip on electrode pad:						
		$\begin{array}{ c c c c c c }\hline y: Chip \ width & x: Chip \ length & z: Chip \ thickness \\\hline y \leq 0.5mm & x \leq 1/8a & 0 < z \leq t \\\hline \end{array}$						
06		6.2.2 Non-conductive portion:						
		y: Chip width x: Chip length z: Chip thickness  y ≤ L x ≤ 1/8a 0 < z ≤ t  Olf the chipped area touches the ITO terminal, over 2/3 of the ITO must remain and be inspected according to electrode terminal specifications.  Olf the product will be heat sealed by the customer, the alignment mark not be damaged.  6.2.3 Substrate protuberance and internal crack.  y: width x: length y ≤ 1/3L x ≤ a						

NO	Item	Criterion			
07	Cracked glass	The LCD with extensive crack is not acceptable.			
08	Backlight e <b>l</b> ements	<ul> <li>8.1 Illumination source flickers when lit.</li> <li>8.2 Spots or scratched that appear when lit must be judged. Using LCD spot, lines and contamination standards.</li> <li>8.3 Backlight doesn't light or color wrong.</li> </ul>			
09	Bezel	<ul><li>9.1 Bezel may not have rust, be deformed or have fingerprints, stains or other contamination.</li><li>9.2 Bezel must comply with job specifications.</li></ul>	2.5 0.65		
10	PCB COB	<ul> <li>10.1 COB seal may not have pinholes larger than 0.2mm or contamination.</li> <li>10.2 COB seal surface may not have pinholes through to the IC.</li> <li>10.3 The height of the COB should not exceed the height indicated in the assembly diagram.</li> <li>10.4 There may not be more than 2mm of sealant outside the seal area on the PCB. And there should be no more than three places.</li> <li>10.5 No oxidation or contamination PCB terminals.</li> <li>10.6 Parts on PCB must be the same as on the production characteristic chart. There should be no wrong parts, missing parts or excess parts.</li> <li>10.7 The jumper on the PCB should conform to the product characteristic chart.</li> <li>10.8 If solder gets on bezel tab pads, LED pad, zebra pad or screw hold pad, make sure it is smoothed down.</li> <li>10.9 The Scraping testing standard for Copper Coating of PCB</li> </ul>			
11	Soldering	<ul> <li>11.1 No un-melted solder paste may be present on the PCB.</li> <li>11.2 No cold solder joints, missing solder connections, oxidation or icicle.</li> <li>11.3 No residue or solder balls on PCB.</li> <li>11.4 No short circuits in components on PCB.</li> </ul>	2.5 2.5 2.5 0.65		

NO	Item	Criterion			
		12.1 No oxidation, contamination, curves or, bends on interface Pin (OLB) of TCP.	2.5		
		12.2 No cracks on interface pin (OLB) of TCP.	0.65		
		12.3 No contamination, solder residue or solder balls on product.	2.5		
		12.4 The IC on the TCP may not be damaged, circuits.	2.5		
		12.5 The uppermost edge of the protective strip on the interface			
		pin must be present or look as if it cause the interface pin to			
12	Genera <b>l</b> appearance	sever.  12.6 The residual rosin or tin oil of soldering (component or chip			
		component) is not burned into brown or black color.	2.5		
		12.7 Sealant on top of the ITO circuit has not hardened.	0.65		
		12.8 Pin type must match type in specification sheet.	0.65		
		12.9 LCD pin loose or missing pins.	0.65		
	N.	12.10 Product packaging must the same as specified on packaging specification sheet.			
		12.11 Product dimension and structure must conform to product	0.65		
		specification sheet.  12.12 Visual defect outside of VA is not considered to be rejection.			

#### **Precautions in use of LCD Modules**

- (1)Avoid applying excessive shocks to the module or making any alterations or modifications to it.
- (2)Don't make extra holes on the printed circuit board, modify its shape or change the components of LCD module.
- (3)Don't disassemble the LCM.
- (4)Don't operate it above the absolute maximum rating.
- (5)Don't drop, bend or twist LCM.
- (6) Soldering: only to the I/O terminals.
- (7) Storage: please storage in anti-static electricity container and clean environment.
- (8) Midas have the right to change the passive components, including R3,R6 & backlight adjust resistors. (Resistors, capacitors and other passive components will have different appearance and color caused by the different supplier.)
- (9) Midas have the right to change the PCB Rev. (In order to satisfy the supplying stability, management optimization and the best product performance...etc, under the premise of not affecting the electrical characteristics and external dimensions, Midas have the right to modify the version.)
- (10) To ensure the stability of the display screen, please apply screen saver after showing 30 mins of fixed display content.
- (11)Please heat up a little the tape sticking on the components when removing it; otherwise the components might be damaged.

#### **Material List of Components for RoHs**

1. Midas Displays hereby declares that all of or part of products (with the mark "#"in code), including, but not limited to, the LCM, accessories or packages, manufactured and/or delivered to your company (including your subsidiaries and affiliated company) directly or indirectly by our company (including our subsidiaries or affiliated companies) do not intentionally contain any of the substances listed in all applicable EU directives and regulations, including the following substances.

Exhibit A: The Harmful Material List

Material	Cd	Pb	Hg	Cr6+	PBB	PBDE	DEHP	BBP	DBP	DIBP
Limited	100	1000	1000	1000	1000	1000	1000	1000	1000	1000
Va <b>l</b> ue	ppm	ppm	ppm	ppm	ppm	ppm	ppm	ppm	ppm	ppm
Above limited value is set up according to RoHS.										

- 2.Process for RoHS requirement : (only for RoHS inspection)
  - (1) Use the Sn/Ag/Cu soldering surface; the surface of Pb-free solder is rougher than we used before.
  - (2) Heat-resistance temp. :

Reflow: 250°C,30 seconds Max.;

Connector soldering wave or hand soldering: 320°C, 10 seconds max.

(3) Temp. curve of reflow, max. Temp.: 235±5°C;

Recommended customer's soldering temp. of connector: 280°C, 3 seconds.

### **Recommendable Storage**

1. Place the panel or module in the temperature 25°C±5°C and the humidity below 65% RH

- 2. Do not place the module near organics solvents or corrosive gases.
- 3. Do not crush, shake, or jolt the module.