

SMBus-Reader

Design-In Tool

P/N: 100122



Features:

- Simple and easy read out of SMBus batteries
- Display information direct from the battery, controlled by only two buttons
- No external PSU required
- Compatible with all SMBus batteries with 5 way blade connector
- All information displayed could be sent via standard RS232 interface to a connected host
- Screen: 16*2

Applications:

The ideal and essential SMBus battery diagnostic tool for development engineers

Following SMBus Quick Info will be shown on the screen

Display information	Value
Start Screen	
Software version	
Send data info	
Battery uses PEC	YES or NO
Time alarm	min
Capacity alarm	mAh
Time to full	min
Time to empty	min
Charging current	mA
Charging voltage	mV
Max. error	%
Cycle count	#
Mode register	Hex
State register	Hex
Design voltage	mV
Design capacity	mAh
Absolut state of charge	%
Full capacity	mAh
Remaining capacity	mAh
Relative state of charge	%
NTC measured	Ohm
Temperature	K and C
Current (SMBus)	mA
Voltage measured	mV
Voltage (SMBus)	mV
Manufacture date	YYYY/MM/DD
Serial number	#
Specification ID	
Chemistry	LION e.g.
Battery name	RRCxxxx e.g.
Manufacturer	RRC e.g.

Mechanical Details	
Dimensions (LxWxH)	94.00 x 58.00 x 25.00mm
Weight	68g

Germany/Headquarters

RRC power solutions GmbH
Technologiepark 1
66424 Homburg / Saar

Tel.: +49 6841 98090
Fax: +49 6841 9809280
Email: sales@rrc-ps.de
Web: www.rrc-ps.de

USA

RRC power solutions Inc.
18340 Yorba Linda Blvd.,
107-437 Yorba Linda,
CA 92886-4104

Tel.: +1 714 777 3604
Fax: +1 714 777 3658
Email: usa@rrc-ps.com
Web: www.rrc-ps.com

Hong Kong

RRC power solutions Ltd.
S-V,6/F, Valiant Industrial
Centre 2-12 Au Pui Wan Street
Fo Tan, N.T., Hong Kong

Tel.: +852 2376 0106
Fax: +852 2375 0107
Email: hkrrc@rrc-ps.cn
Web: www.rrc-ps.com

China

RRC power solutions Ltd.
Room 1306, C Building,
Tianan International building,
Renmin South Road, Luohu
District, Shenzhen 518021

Tel.: +86 755 8374 1908
Fax: +86 755 8374 1861
Email: hkrrc@rrc-ps.cn
Web: www.rrc-ps.com