

SPECIFICATION SHEET

EMERGENCY MAINTAINED/ NON-MAINTAINED LED BULKHEAD




The new Emergency Maintained / Non-Maintained LED Bulkhead has a single 3.5W LED strip that produces 150 lumens in standard and 110 lumens in emergency. It comes with a hinged gear tray and screw terminal connector, for ease of installation.

Applications

- Multi-Storey Carparks • Leisure Centres • Hospitality



Dimensions



Specification

| | |
|-----------------------------|---------------------------------|
| LED: | 27pcs of 2835 LED |
| Material: | Polycarbonate |
| Lumen Output: | 150lm (110lm in emergency mode) |
| Colour Temperature: | 6500K |
| Guarantee: | 3 Years |
| Working Temperature: | 5°C - 25°C. |
| Power Factor: | 0.45 |
| Beam Angle: | 110° |
| CRI: | 80 Ra |

Additional Information

- 3.6V 1000mAh Ni-Cd Battery included
- 43lm/W
- White finish
- Includes Multi-Directional Sticker Legend Kit
- Over-charge and deep-discharge protection
- 4 x 20mm entry points

| Code | Wattage | Dimensions (L x W x D mm) |
|-----------|---------|---------------------------|
| LFACLED-2 | 3.5W | 350 x 110 x 65 |