


PRODUCT NUMBER: 7945-2-15-20-09-14-11-0



DESCRIPTION

Spring-Loaded Pin with a Standard Tail

Durability:

100,000 to 1,000,000 Cycles

Current Rating:

5.5A @ 30°C Temperature Rise

Contact Resistance:

20 mΩ Max

Operating Temperature Range:

-55/+125° C (discontinuous)

Vibration:

No Elect. Discontinuity > 1μs @ 10-2000HZ, 20 G

Shock:

No Elect. Discontinuity > 1μs @ 50g

Mounting Feature:

Through-Hole Solder Mount

Tail Type: Soldertail

Mounting Hole: .044" (1,118mm)

Tail Diameter: .040" (1,016mm)

Packaging: 15 - Packaged in Bulk

| | | |
|----------------------|-----------------------|-------------|
| Shell Plating | Spring Plating | ROHS |
|----------------------|-----------------------|-------------|

20 μ" Gold over Nickel

10 μ" Gold over Nickel




SPRING:

#09 SPRING

STANDARD FORCE SPRING: 55 GRAMS FORCE
@ MID STROKE; .030" FULL STROKE

| |
|---|
| Spring Material : Beryllium Copper Alloy 172 |
| Mid. Stroke : .015" [0,38] |
| Full Stroke Capability : .030" ± .005" [0,76 ± 0,127] |
| Force @ Mid. Stroke : 55 g ± 10 g |
| Initial Force (Pre-Load) : 30 g |



Stroke & force values are measured using spring pins with an internal construction per the design specification.
Individual spring pin performance may vary from these values based on design differences.

| | | | |
|------------|------------------|-------------|----|
| Material | Beryllium Copper | Grams Force | 55 |
| Max Stroke | 0.03 | | |

CONTACT MATERIAL:

BERYLLIUM COPPER ALLOY 172 (UNS C17200) per ASTM B 194

Properties of BERYLLIUM COPPER:

- Chemical composition: Cu 98.1%, Be 1.9%
- Hardness: 36-43 Rockwell C
- Density: .298 lbs/in³
- Electrical Conductivity: 22% IACS*
- Resistance: 10 mΩ Max
- Operating Temperature: -55°C/+125°C
- Melting point: 980°C/865°C (liquidus/solidus)
- Stress Relaxation†: 96% of stress remains after 1,000 hours @ 100 °C; 70% of stress remains after 1,000 hours @ 200 °C

*International Annealed Copper Standard, i.e. as a % of pure copper.

†Since BeCu loses its spring properties over time at high temperatures; it is rated for continuous use up to 150 °C. For applications up to 300 °C, Mill-Max offers other materials. [Contact Tech Support](#) for more info.

ADDITIONAL NOTES & SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

© 2020 Mill-Max Mfg. Corp.
190 Pine Hollow Rd , Oyster Bay, NY 11771, USA
Phone: 516.922.6000