Toggle Switch

multicomp PRO



Feature:


· Epoxy sealed terminations

Specifications:

Electrical Life Contact Resistance	 : 40,000 make-and-break cycles at full load : 10mΩ max. initial at 2 - 4V DC 100mA for both silver and gold plated contacts 		
Insulation Resistance	: $1,000M\Omega$ min.		
Dielectric Strength	: 1,000V RMS at sea level		
Operating Temperature	: -30°C to +85°C		
Materials:			
Case	: Dially phthalate (DAP)		
Actuator	: Brass, Chrome plated		
Bushing	: Brass, Nickel plated		
Housing	: Stainless Steel		
Terminal/Contact	: Silver or gold plated		
Rating:			
R	: 0.4 Volt-Amps (VA) maximum at 20V maximum (AC or DC).		
Q	: 2A at 250V AC		

5A at 120V AC or 28V DC

Diagram



Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

multicomp PRO

Part Number Table

Description	Туре	Bush Thread	Lever Length	Part Number
Flat Toggle	SPDT mom-off-mom	1/4" × 40 NS	10.4	1MS4T6B11M1QE

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

