

PRO-ELEC



Hand Dryer
Models: PELB0036

IMPORTANT SAFETY INFORMATION

When using electrical appliances, basic safety precautions should always be followed to reduce the risk of fire, electric shock and injury to persons or property.

Read all instructions before using the appliance and retain for future reference.

- Check that the voltage indicated on the rating plate corresponds with that of the local network before connecting the appliance to the mains power supply.
- This appliance is designed for indoor use only.
- There are no user-serviceable parts in this product. Refer servicing to qualified personnel.
- Do not operate this appliance with a damaged cord, after a malfunction or after being dropped or damaged in any way.
- If the supply cord is damaged, it must be replaced by the manufacturer, its service agent or similarly qualified persons in order to avoid a hazard.
- This appliance can be used by children aged from 8 years and above and persons with reduced physical, sensory, or mental capabilities or lack of experience and knowledge if they have been given supervision or instruction concerning use of the appliance in a safe way and understand the hazards involved.
- Children shall not play with the appliance.
- Cleaning and maintenance shall not be made by children without supervision.
- Do not block the air inlet or outlet as this will cause the dryer to overheat.
- Do not place the dryer near to soft furnishings as this may cause damage to them, and could cause the dryer to overheat.
- This product must be earthed.

WARNING: Do not use this appliance near bathtubs, showers, basins or other vessels containing water.


WHAT'S INCLUDED

- Hand dryer
- User manual
- Installation template
- Pack of 3 screws and 3 wall plugs
- Hook mounting

PRODUCT OVERVIEW

Main Features


- The hand dryer uses digital circuit control and infra red sensor with protection against overheating.
- Energy saving high speed/low power motor with high efficiency nozzle.




1. Outer casing
2. Nozzle
3. Lamp
4. Sensor
5. Sealing plate
6. Mounting block
7. Mounting hook

INSTALLATION

- This product must be installed in accordance with the IET Wiring Regulations (BS7671) and the Building Regulations. In any doubt, contact a qualified electrician.
- The recommended installation height (measured from air outlet to the floor) 1.2m for men, 1.1m for women, and 0.9m for children.
- The electrical connection must be made using a double pole isolating switch with a break contact distance of at least 3mm.
- Using the supplied template mark the three mounting holes on the wall with reference to the above height requirements and the location of the power supply.




- Ensure the surface is able to support the weight of the dryer.
- Drill the three holes having checked first that there are no concealed cables or pipework, and fit the wall plugs.
- Remove the cross head screw in the lower mounting block, and remove the block from the dryer.



- Attach the mounting block to the wall using two of the screws provided into the previously drilled lower holes, so that the cable channel is on the left side.

- Attach the upper mounting hook to the wall using the screw provided into the remaining hole so that the screw head sits flush into the recess in the hook.

- Offer the dryer to the wall and make sure the cable sits in the channel in the mounting block, then lower the dryer so that the hook and mounting block engage with the dryer casing.



- When the dryer is in place refit the cross head screw through the bottom mounting block to lock the dryer in position.
- If you are using a concealed mains cable, before attaching the dryer to the fixed wall mounts, remove the bottom cover by unscrewing the small cross head screw and disconnect and remove supplied mains cable with 13A plug from the connector block and the cable retention clamp.
- Ensure the supply is isolated then feed the concealed supply cable into the slot in the casing then after lowering the dryer into position and fitting the retaining screw, fit the cable retention clamp and trim the length and connect the mains wires to the terminal block as follows:

Red or brown wire to the terminal marked L

Black or blue wire to the terminal marked N

Green or green/yellow to the terminal marked \perp


- Refit the cover and tighten the screw.
- Connect the mains plug or restore the mains power.

APPLICATION

- After finishing the installation, and switching on the power, and the hand dryer will switch on automatically when hands are placed underneath the air outlet.
- The hand dryer blows the hot air when hands are 10cm or closer to the air outlet, and it stops working 1 second after removing hands. It will also stop working automatically after 1 minute consecutive use. To restart the hand dryer, put hands back underneath and the dryer will switch on again.

SPECIFICATIONS

Voltage	Power	Frequency	Water splash proof	Airflow
220-240V~	1200W	50/60Hz	IP22	97m/s 114 ³ m/h



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

Made in China. PR2 9PP

Man Rev 1.0

