

PRODUCT-DETAILS

## CT-ARC.12

CT-ARC.12 Time relay, Dual function 1c/o, 24-48VDC/24-240VAC, w/o aux.supply



### General Information

Extended Product Type	CT-ARC.12
Product ID	1SVR508120R0000
EAN	4013614555633
Catalog Description	CT-ARC.12 Time relay, Dual function 1c/o, 24-48VDC/24-240VAC, w/o aux.supply
Long Description	CT-ARC.12 Time relay, Dual function 1c/o, 24-48VDC/24-240VAC, w/o aux.supply

### Ordering

EAN	4013614555633
Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

### Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	89 mm
Package Level 1 Depth / Length	20 mm
Package Level 1 Height	65 mm
Package Level 1 Gross Weight	0.065 kg
Package Level 1 EAN	4013614555633

## Dimensions

Product Net Width	17.5 mm
Product Net Height	70 mm
Product Net Depth / Length	63 mm
Product Net Weight	0.053 kg

## Technical

Timer Relay Type	Impulse OFF True OFF-Delay
Time Range	0.05 s ... 10 min
Rated Control Supply Voltage (U <sub>s</sub> )	24 ... 240 V AC 24 ... 48 V DC
Rated Frequency (f)	50 Hz 60 Hz DC
Output	1 c/o (SPDT) contact
Terminal Type	Screw Terminals
Rated Operational Current AC-12 (I <sub>e</sub> )	(230 V) 4 A
Rated Operational Current AC-15 (I <sub>e</sub> )	(230 V) 3 A
Rated Operational Current DC-12 (I <sub>e</sub> )	(24 V) 4 A
Rated Operational Current DC-13 (I <sub>e</sub> )	(24 V) 1.5 A
Minimum Switching Capacity	12 V 100 mA
Rated Insulation Voltage (U <sub>i</sub> )	Input Circuit / Output Circuit 300 V
Degree of Protection	Housing IP50 Terminals IP20
Overvoltage Category	III
Pollution Degree	3
Short-Circuit Protective Devices	Output Circuit NC - F Type Fuses 6 A Output Circuit NO - F Type Fuses 10 A
Connecting Capacity	Flexible 1x 0.5 ... 2.5 mm <sup>2</sup> Flexible 2x 0.5 ... 1.5 mm <sup>2</sup> Rigid 1x 0.5 ... 4 mm <sup>2</sup> Rigid 2x 0.5 ... 1.5 mm <sup>2</sup>
Tightening Torque	0.5 ... 0.8 N·m
Wire Stripping Length	7 mm
Mounting Position	Any
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Standards	CAN/CSA C22.2 No.14 EN 50581 IEC/EN 61812-1 UL 508

## Environmental

Ambient Air Temperature	Operation -20 ... +60 °C Storage -40 ... +85 °C
RoHS Status	Following EU Directive 2011/65/EU

## Technical UL/CSA

Maximum Operating	Output Circuit 300 V AC
-------------------	-------------------------

Voltage UL/CSA	
Contact Rating UL/CSA	B300
Connecting Capacity UL/CSA	Flexible 1x 18-14 AWG Flexible 2x 18-16 AWG Rigid 1x 20-12 AWG Rigid 2x 20-16 AWG
Tightening Torque UL/CSA	4.43 ... 7.08 in-lb

## Certificates and Declarations (Document Number)

CCC Certificate	CCC_2019010303150608
cULus Certificate	cULus_20031209-E140448
Data Sheet, Technical Information	2CDC111163C0201
Declaration of Conformity - CE	1SVD981068
Instructions and Manuals	1SVC500020M0001
RoHS Information	1SVD981068

## Classifications

Object Classification Code	K
ETIM 5	EC001439 - Timer relay
ETIM 6	EC001439 - Timer relay
ETIM 7	EC001439 - Timer relay
eClass	7.0 27371790
UNSPSC	39121519

## Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Time Relays

