


# GEFORCE® GT 1030 2GH LP OC



## SPECIFICATION

<b>Model Name</b>	GeForce® GT 1030 2GH LP OC
<b>Graphics Processing Unit</b>	NVIDIA® GeForce® GT 1030
<b>Interface</b>	PCI Express 3.0 x16 (uses x4)
<b>Cores</b>	384 Units
<b>Core Clocks</b>	1518 MHz / 1265 MHz
<b>Memory Speed</b>	6008 MHz
<b>Memory</b>	2GB GDDR5
<b>Memory Bus</b>	64-bit
<b>Output</b>	HDMI 2.0b / DisplayPort (Version 1.4)
<b>HDCP Support</b>	2.2
<b>Power consumption</b>	30 W
<b>Recommended PSU</b>	300 W
<b>Card Dimension (mm)</b>	153 x 69 x 38 mm
<b>Weight (Card / Package)</b>	302 g / 542 g
<b>DirectX Version Support</b>	12
<b>OpenGL Version Support</b>	4.5
<b>Maximum Displays</b>	2
<b>Accessories</b>	Low Profile Bracket x 1 (DisplayPort / HDMI)

## CONNECTIONS



1. HDMI
2. DisplayPort

## FEATURE

### All Solid Capacitors

- 10 years long lifetime under full load.
- Aluminum core for higher stability.

### Low Profile Design

- Low profile design saves more spaces.
- User can build slim or smaller system.

### Virtually Silent

- Large heat sink covers the area of GPU and memory.
- Providing the best environment for gaming and multimedia.

### Afterburner Overclocking Utility

- Wireless control through mobile devices.
- Predator: In-game video recording.

### GeForce Experience

- Ensures the best gaming experience by automatically updating users' game-ready drivers.
- Allows users to optimize the game settings to their PC with a single click.