

LOCTITE[®] Si 5611™

July 2013

PRODUCT DESCRIPTION

 $\text{LOCTITE}^{\textcircled{8}}$ Si 5611 $^{\texttt{M}}$ provides the following product characteristics:

Technology	Silicone
Chemical Type	Alkoxy silicone
Appearance, Resin (Component A)	White liquid
Appearance, Hardener (Component B)	Black liquid
Appearance (Mixture)	Grey Liquid
Components	Two component - requires mixing
Mix Ratio, by volume - Part A: Part B	10 : 1
Cure	Room temperature cure and Atmospheric moisture
Application	Bonding and Sealing

LOCTITE[®] Si 5611[™] is a two part, fast cure, low viscosity / self leveling silicone. This product is designed for applications that require a fast cure. LOCTITE[®] Si 5611[™] is neutral curing and non-corrosive. Typical applications include solar, lighting, switches, and electronic connectors.

UL Classification

LOCTITE[®] Si 5611^m is listed in UL's recognized component index with 94V-0 flammability rating in 6.8mm, 9.0mm thickness cross section

TYPICAL PROPERTIES OF UNCURED MATERIAL

Part A:	
Specific Gravity @ 25 °C	1.34
Flash Point - See MSDS Viscosity, Cone & Plate, 25 °C, mPa·s (cP): Spindle 20, Speed 20 s ⁻¹	3,500 to 10,000
Part B:	
Specific Gravity @ 25 °C	1.08
Viscosity, Cone & Plate, 25 °C, mPa·s (cP): Spindle 20, Speed 20 s ⁻¹	3,000 to 10,000
Mixed:	
Specific Gravity @ 25 °C	1.22
Tack Free Time, minutes	6
Slump Test, minutes Time at which No Slump occurs	≤15

Flash Point - See MSDS

TYPICAL CURING PERFORMANCE

The mix of part A and part B initiates the reaction. There is a secondary cure with atmospheric moisture that promotes full cure over 7 days.

Skin Over Time

Skin over time is the time the surface of the adhesive forms a skin upon exposure to atmospheric moisture at 25 ± 2 °C, $50 \pm 5\%$ RH.

Skin Over Time, minutes

6 to 18

Cure Speed vs. Time

The graph below shows the shear strength developed over time at 22 $^\circ C$ / 50 % RH on aluminum (Alclad) and tested according to ISO 4587.



TYPICAL PROPERTIES OF CURED MATERIAL

Cured for 24 hours @ 22±3 °C / 50±20% RH Physical Properties : Shore Hardness, ISO 868, Durometer A		≥50
Cured for 7 days @ 22 °C / 50% RH Physical Properties:		
Glass Transition Temperature (Tg), °C		-57
Elongation, at break, ISO 527-3, %		59
Tensile Strength, ISO 527-3	N/mm² (psi)	2 (290)
Tensile Modulus, at 50% elongation	N/mm² (psi)	1.8 (260)
Tear Strength, ISO 34-1 , Die C	N/mm (lb./in.)	3.7 (21)



Water Absorption, ISO 62, %:	
24 hours in water @ 22 °C:	
Increased weight	0.55
Soluble matter loss	0.13
Coefficient of Thermal Conductivity, W/(m·K)	0.32
Coefficient of Thermal Expansion, ISO 11359-2, K ⁻¹ :	
Post Tg	235×10 ⁻⁶
Volume Shrinkage, %	7.7
Linear Shrinkage, %	2.63

Electrical Properties:

Dielectric Constant / Dissipation Factor, IEC	60250:
1 kHz	3.877 / 0.0448
1 MHz	3.655 / 0.0131
Volume Resistivity, IEC 60093, Ω·cm	3.5×10 ¹⁴
Dielectric Breakdown Strength,	19.8
IEC 60243-1, kV/mm	

TYPICAL PERFORMANCE OF CURED MATERIAL

Cured for 7 days @ 22 °C / 50% RH, 0 gap

Adhesive Properties

"T" Peel Strength, ISO 11339: PVF	N/mm (Ib/in)	0.3 (1.7)
Shear Strength:		
Lap Shear Strength, ISO 4587:		
Steel (degreased)	N/mm²	0.9
	(psi)	(140)
Stainless steel	N/mm²	0.7
	(psi)	(110)
Alclad	N/mm ²	1.0
A.L	(psi)	(150)
Aluminum	N/mm²	0.4
01	(psi)	(65)
Glass	IN/IIIII-	(100)
D)/C	(psi) N/mm²	(100)
FVC	(nsi)	(170)
Acordia	N/mm ²	0.2
Acrylic	(nsi)	(25)
Polycarbonate	N/mm ²	0.6
i olycarbonato	(psi)	(90)
Nvlon	N/mm ²	0.4
, -	(psi)	(60)
PPO	N/mm²	0.5
	(psi)	(70)

TYPICAL ENVIRONMENTAL RESISTANCE

Lap Shear Strength, ISO 4587: Alclad



Heat Aging

Cured for 7 days @ 22 °C and Tested at temperature

Aged @ 100 °C for 1,000 hours:	
Change in Tensile Strength, %	36
Change in Elongation, %	25
Aged @ 150 °C for 1,000 hours:	
Change in Tensile Strength, %	108
Change in Elongation, %	8
Aged @ 200 °C for 1,000 hours:	
Change in Tensile Strength, %	90
Change in Elongation, %	-48

Chemical/Solvent Resistance

Cured for 7 days @ 22 °C

Tensile Strength, ISO 527-3,

		% of initial strength	
Environment	°C	500 h	1000 h
Water	22	100	100
Isopropanol	22	80	80
2% Ammonia/Water	22	100	100
Motor oil (10W30)	22	120	120
Water/glycol 50/50	22	100	100
85% RH	85	80	20

Elongation, ISO 527-3

		% of initial strength	
Environment	°C	500 h	1000 h
Water	22	100	100
Isopropanol	22	170	125
2% Ammonia/Water	22	120	120
Motor oil (10W30)	22	175	125
Water/glycol 50/50	22	145	145
85% RH	85	275	75

GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Material Safety Data Sheet (MSDS).

Directions for use:

- 1. For high strength structural bonds, remove surface contaminants such as paint, oxide films, oils, dust, mold release agents and all other surface contaminants.
- 2. Use gloves to minimize skin contact. DO NOT use solvents for cleaning hands.
- 3. **Dual Cartridges:** To begin using a new cartridge, remove cartridge cap and dispense a small amount of adhesive, making sure both parts A&B are extruding. Attach nozzle and dispense approximately 25 to 50mm, before applying onto part to be bonded. Partially used cartridges can be stored with the mixing nozzle attached. To reuse, remove and discard old nozzle, attach the new nozzle, dispense approximately 25 to 50mm, before applying onto part to be bonded.

Bulk Containers: Normally material is dispensed through volumetric metered mixing equipment, attached to static mix nozzles.

- 4. Application to the substrates should be made as soon as possible. Larger quantities and/or higher temperatures will reduce the working time.
- 5. Keep assembled parts from moving during cure. The bond should be allowed to develop full strength before subjecting to any service load.
- 6. Excess material can be easily wiped away with non-polar solvents.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 8 °C to 21 °C. **Storage below 8** °C or **greater than 28** °C **can adversely affect product properties**. Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

 $(^{\circ}C \ge 1.8) + 32 = ^{\circ}F$ kV/mm x 25.4 = V/mil mm / 25.4 = inches μ m / 25.4 = mil N x 0.225 = lb N/mm x 5.71 = lb/in N/mm² x 145 = psi MPa x 145 = psi N·m x 8.851 = lb·in N·m x 0.738 = lb·ft N·mm x 0.142 = oz·in mPa·s = cP

Disclaimer

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits. The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. $^{\textcircled{0}}$ denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.0