

LOCTITE<sup>®</sup> AA 3298™

Known as LOCTITE<sup>®</sup> 3298™ June 2014

#### PRODUCT DESCRIPTION

LOCTITE<sup>®</sup> AA 3298<sup>™</sup> provides the following product characteristics:

Technology	Acrylic
Chemical Type	Modified methacrylate ester
Appearance (uncured)	Straw yellow to brown liquid <sup>LMS</sup>
Components	One component -
	requires no mixing
Viscosity	Medium
Cure	Anaerobic with activator
Application	Bonding
Strength	High

LOCTITE<sup>®</sup> AA 3298<sup>TM</sup> is a toughened acrylic adhesive material intended for high strength structural bonding. This product incorporates a silane coupling agent which ensures good bond durability on glass surfaces. It cures at ambient temperature with the aid of Activators  $737^{TM}$ ,  $738^{TM}/7386^{TM}$  or  $740^{TM}/7407^{TM}$ . LOCTITE<sup>®</sup> AA 3298<sup>TM</sup> is suitable for bonding a range of materials, including sheet metal and glass, where continuous or repeated loading is encountered (e.g. furniture, containers, doors).

#### TYPICAL PROPERTIES OF UNCURED MATERIAL

Specific Gravity @ 25 °C 1.02


Flash Point - See SDS

Viscosity, Brookfield - RVT, 25 °C, mPa·s (cP): Spindle 6, speed 20 rpm, 17,000 to 41,000<sup>LMS</sup>

#### TYPICAL CURING PERFORMANCE


#### Cure Speed vs. Substrate

The rate of cure will depend on the substrate used. The graph below shows the shear strength developed with time on grit blasted steel lap shears compared to different materials and tested according to ISO 4587.



#### Cure Speed vs. Bond Gap


The rate of cure will depend on the bondline gap. The following graph shows the shear strength developed with time on grit blasted steel lap shears at different controlled gaps and tested according to ISO 4587.



#### Cure Speed vs. Activator

An activator must be used to ensure cure of this product. The rate of the cure will depend on the activator used. In general, Activator 737<sup>TM</sup> is recommended for optimum durability or where large bond gaps are present. For fastest fixturing and where gaps are less than 0.1 mm, Activator 740<sup>TM</sup> is recommended. For non-metallic surfaces, Activators 738<sup>TM</sup> and 740<sup>TM</sup> are preferred. The graph below shows the shear strength developed with time on PVC lap shears with different activators.





#### TYPICAL PROPERTIES OF CURED MATERIAL

#### **Physical Properties:**

Coefficient of Thermal Expansion, ISO 11359-2. K <sup>-1</sup>	100×10⁻ <sup>6</sup>
Coefficient of Thermal Conductivity, ISO 8302, W/(m·K)	0.1
Specific Heat, kJ/(kg·K)	0.3


#### TYPICAL PERFORMANCE OF CURED MATERIAL Adhesive Properties

Cured for 24 hours @ 22 °C, Activator 7386™ on 1 side

Lap Shear Strength, ISO 4587: Stainless steel (grit blasted)	N/mm² (psi)	≥21.5 <sup>∟MS</sup> (≥3,117)
	(poi)	(=0,111)
Cured for 24 hours @ 22 °C, Activa	tor 737™	
Lap Shear Strength, ISO 4587:		
Steel (grit blasted)		26 to 32
	. ,	(3,770 to 4,640)
Aluminum	N/mm² (psi)	8 to 20 (1,160 to 2,900)
	(psi)	(1,100 to 2,900)
Tensile Strength, ISO 6922:		
Steel (grit blasted)		15 to 27
	. ,	(2,175 to 3,900)
Steel (grit blasted) to Glass		11 to 26
	(psi)	(1,600 to 3,770)
"T" Peel Strength, ISO 11339:		•
Aluminum (grit blasted)		0 6 2 to 24)
	(lb/in) (22	2 to 34)


#### TYPICAL ENVIRONMENTAL RESISTANCE

Cured for 1 week @ 22 °C, Activator 737™ Lap Shear Strength, ISO 4587: Steel (grit blasted)



#### **Heat Aging**

Aged at temperature indicated and tested @ 22 °C



#### Chemical/Solvent Resistance

Aged under conditions indicated and tested @ 22 °C

		% of initial strength		
Environment	°C	100 h	500 h	1000 h
Motor oil (MIL-L-46152)	125	100	100	100
Acetone	22	95	90	80

Tensile Strength, ISO 6922:

Steel pin (grit blasted) to Glass

		% of initial strength		
Environment	°C	100 h	500 h	1000 h
95% RH	40	90	45	45

#### **GENERAL INFORMATION**

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

## For safe handling information on this product, consult the Safety Data Sheet (SDS).

Where aqueous washing systems are used to clean the surfaces before bonding, it is important to check for compatibility of the washing solution with the adhesive. In some cases these aqueous washes can affect the cure and performance of the adhesive.

This product is not normally recommended for use on plastics (particularly thermoplastic materials where stress cracking of the plastic could result). Users are recommended to confirm compatibility of the product with such substrates.

#### Directions for use:

- 1. For best performance bond surfaces should be clean and free from grease.
- 2. To ensure a fast and reliable cure, Activator 737<sup>™</sup> or 7386<sup>™</sup> should be applied to one of the bond surfaces and the adhesive to the other surface. Parts should be assembled within 15 minutes.
- 3. The recommended bondline gap is 0.05 mm. Where bond gaps are large (up to a maximum of 0.4 mm), or faster cure speed is required, Activator 737<sup>™</sup> or 7386<sup>™</sup> should be applied to both surfaces. Parts should be assembled immediately (within 1 minute).
- 4. Excess adhesive can be wiped away with organic solvent.
- 5. Bond should be held clamped until adhesive has fixtured.
- 6. Product should be allowed to develop full strength before subjecting to any service loads (typically 24 to 72 hours after assembly, depending on bond gap, materials and ambient conditions).

#### Loctite Material Specification

LMS dated November 21, 2012. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.

#### Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

**Optimal Storage: 2 °C to 8 °C. Storage below 2 °C or greater than 8 °C can adversely affect product properties.** Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

#### Conversions

 $(^{\circ}C \times 1.8) + 32 = ^{\circ}F$ kV/mm x 25.4 = V/mil mm / 25.4 = inches  $\mu$ m / 25.4 = mil N x 0.225 = lb N/mm x 5.71 = lb/in N/mm<sup>2</sup> x 145 = psi MPa x 145 = psi N·m x 8.851 = lb·in N·m x 0.738 = lb·ft N·mm x 0.142 = oz·in mPa·s = cP

#### Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

# In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

### In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

#### In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits. The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

#### Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. <sup>®</sup> denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1.2