

TEROSON MS 9380

October 2019

PRODUCT DESCRIPTION

TEROSON MS 9380 provides the following product characteristics:

Technology	Silane-modified polymer
Product Type	Adhesive
Components	One-component
Cure	Humidity
Application	Assembly
Appearance	White, Grey, Black
Consistency	Pasty, Thixotropic
Odor	Characteristic

TEROSON MS 9380 is a high viscosity, sag resistant one component adhesive based on silane modified polymer, which cures by reaction with moisture to an elastic product. The skin formation and curing times are dependent on humidity and temperature, and the curing time also depends on joint depth. By increasing the temperature and moisture these times can be reduced; low temperature as well as low moisture retard the process. . TEROSON MS 9380 is free of solvents, isocyanates, silicones and PVC. . It demonstrates good adhesion to many substrates. The sealant also demonstrates good UV resistance and can therefore be used for interior and exterior applications. TEROSON MS 9380 allows accelerated curing as two-component material.

Application Areas:

TEROSON MS 9380 can be used for the following applications:

elastic bonding of metals and plastics, e.g. side panelling and bonding of the roof skin in the vehicle and caravan manufacture. elastic, interior and/or exterior seam and joint sealing in the following areas. vehicle body, caravan, railway carriage, container and general metal construction; electrical, plastics, air- conditioning and ventilation industries

TECHNICAL DATA

Density, g/cm ³ :	approx. 1.45
Sag resistance:	no sagging (DIN profile 15 mm)
Skin formation time, min*:	approx. 4 to 10
Cure rate, mm/24 hrs:	approx. 3
Shore-A-hardness (ISO 868, Durometer A):	approx. 70
Tensile strength (acc. to ISO 37), MPa:	approx. 4.0
Elongation at break (acc. to ISO 37, speed 200 mm/min),%:	approx. 120
Stress at 100 % elongation (acc. to ISO 37), MPa:	approx. 3.2
Volume change (acc. to DIN 52451), %:	<2
Tensile shear strength	2.0

(acc. to ISO 4587), MPa:

Substrates:	AlMg1SiCu, AlMg2.5
Layer thickness, mm:	2
Cross head speed, mm/min:	10
UV resistance:	no signif. changes
UV source:	Osram Vitalux 300W, dry UV
Distance to the specimen, cm:	25
Test period, weeks:	6
Application temperature, °C:	5 to 40
In service temperature range, °C:	-40 to +100
Short exposure (up to 1 h), °C:	120
* ISO 291 standard climate:	23°C, 50% relative air humidity

DIRECTIONS OF USE

Preliminary Statement:

Prior to application it is necessary to read the **Material Safety Data Sheet** for information about precautionary measures and safety recommendations. Also, for chemical products exempt from compulsory labeling, the relevant precautions should always be observed.

Pre-Treatment:

The substrates must be clean, dry, oil- and grease free. Depending on the surface it can be necessary to roughen the surface or to use a primer/adhesion promoter to provide best adhesion. . When manufacturing plastics, external release agents are often used; these agents must be accurately removed prior to starting bonding or sealing. Due to the different compositions of paints, especially powder paints and the large number of different substrates, application trials before use are necessary. For cleaning, TEROSON VR 10 or TEROSON SB 450 from the Henkel portfolio are suitable. . When bonding and sealing PMMA, e.g. Plexiglas®, and polycarbonate, e.g. Makrolon® or Lexan®, under tension, stress corrosion cracking may occur. Application trials before use are necessary. There is no adhesion to polyethylene, polypropylene and PTFE (e.g. Teflon®). Substrates not mentioned above should be subject to trials.

Application:

Application from 290 mL cartridges is made with the TEROSON Hand or Air Pressure Pistols, and from foil cartridges (310 and 570 mL) with the corresponding FK-Hand or FK-Air Pressure Pistols. In the case of compressed air application a pressure of 2 to 3 bar is required. Low material



temperatures of the sealant will lead to an increase of viscosity, resulting in a lower extrusion rate. This can be avoided by bringing the sealant up to room temperature prior to application. TEROSON MS 9380 can also be applied from hobbicks or drums with high pressure pumps with follower plates.

Cleaning:

For cleaning application equipment contaminated with uncured TEROSON MS 9380 we recommend the use of TEROSON VR 10.

Classification:

Please refer to the corresponding **Material Safety Data Sheets** for details on:

Hazards identification
Transport information
Regulatory information

Storage:

Frost-Sensitive	No
Recommended storage temperature, °C	10 to 25
Shelf-life (in unopened original packaging), 12 months	

ADDITIONAL INFORMATION

Disclaimer:

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 0.2