

Cat 5E Shielded Twisted Paired LSZH Cable

multicomp PRO

RoHS
Compliant



Application:

This cable is used for horizontal wiring in a local area network (LAN) in areas requiring mechanical protection.

Cable Standards:

Made in accordance with the following:

ISO/IEC 11801, TIA/EIA 568B

Construction:

Conductor	: Class 1 solid copper conductor
Insulation	: Solid PE (Polyethylene)
Drain Wire	: Tinned copper
Screen	: AL-Foil (Aluminium Foil)
Bedding	: LSZH (Low Smoke Zero Halogen)
Braiding	: GSWB (Galvanised Steel Wire Braid)
Sheath	: LSZH (Low Smoke Zero Halogen)

Characteristics:

Temperature Rating	: 0°C to +70°C
Min. Bending Radius	: 6 × overall diameter
Core Identification	: Pair 1: Blue and White/Blue Pair 2: Orange and White/Orange Pair 3: Green and White/Green Pair 4: Brown and White/Brown
Sheath Colour	: Black

Electrical Characteristics:

Impedance (1 - 100MHz)	: 100Ω ±15
Max. Resistance of Conductor at 20°C	: 101.2Ω/km

Frequency MHz	Attenuation dB/100m	Next dB	RL dB	ELFEXT dB	PS-ELFEXT dB/100m	ACR dB
1	2	65.3	23.1	63.8	60.8	63
4	4.1	56.3	23	51.7	48.7	51
8	5.8	51.8	24.5	45.7	42.7	45
10	6.5	50.3	25	43.8	40.8	43
16	8.2	47.3	25	39.7	36.7	37
20	9.3	45.8	25	37.7	34.7	35
25	10.23	44.3	24.2	35.8	32.8	32

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Cat 5E Shielded Twisted Paired LSZH Cable

multicomp PRO

Frequency MHz	Attenuation dB/100m	Next dB	RL dB	ELFEXT dB	PS-ELFEXT dB/100m	ACR dB
31.25	11.71	42.9	23.3	33.9	30.9	29
62.5	17.25	38.4	20.7	27.8	24.8	19
100	22	35.3	19.24	23.8	20.8	9

Dimensions:

No. of Pairs (24 AWG)	Nominal Thickness of Insulation	Nominal Overall Diameter	Nominal Weight kg/km
4	1.04mm	9.4mm	124

Part Number Table

Description	Reel Length (m)	Part Number
Cat 5E shielded Twisted Paired LSZH Cable	50	PP000860

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO