


Cable Installation System : Cable Scout Cam

Inspection camera - wireless image and video transmission via WiFi, Article number: 897-90060

 Add to watchlist



 Images (7)



Features

- Accessory kit includes useful tools as hook, magnet and mirror and a watertight cap.
- System compatibility: Android 4.2 and above, iOS, Windows, Mac
- Splash proof according to IP68 (lens tube only with supplied lens cover)
- View Angle: 70°
- Resolution: 2.0 megapixel
- Cable length: 10 m
- Cable type: Semi rigid
- Focal distance: 4-8 cm
- Camera head diameter: 8 mm
- Frequency: 2.4 GHz
- dimmable LED Light

Certifications & Approvals

RoHS 

Application

The Cable Scout Cam HD miniature inspection camera with WiFi transmitter is primarily intended for the visual inspection of inaccessible areas such as conduits, shafts, suspended ceilings, or drywall.

More products in this product group

[Cable Installation System >](#)

Base Data

Application 2

Cable Scout+ comes with many useful accessories. Cable Grips are designed to grip objects from the outside and provide a very reliable super fast method for securing pipes and cables to the rods. Just open a grip by compressing the braided sleeving, push it over a cable and let go, the material will contract immediately and establish a tight grip of the cable to the tool.

Distributors 

Black (BK)

Contact 

Features and Benefits	Due to the wide range of innovative accessories and different flexibilities the Rod Sets are perfectly suited for many different applications.
Flexibility	medium
Pack Cont.	1
Package Quantity per	pcs.
PART DESCRIPTION	Cable Scout Cam-DIV-BK
Product Family	Cable Scout Cam
Product Group	Cable Installation System
Short Description	Inspection camera - wireless image and video transmission via WiFi

Material and Specifications



ELV compliant Dir. Art. 4 (2)	YES
Halogenfree	No
Hazardous good	No
Material	Various (DIV)
Operating Temperature - °C	0 °C to +40 °C
Specifications	

Logistics and Packaging



More Information



ETIM 6.0	EC003007
ETIM 7.0 Key	EC003007

© HellermannTyton 2020