

EXP-4CHN-2BUL-5MP-1

4CHN 2CAM 5MP Bullet



RECORDER FEATURES:

- H.265+/H.265 dual-stream video compression
- Supports HDCVI/AHD/TVI/CVBS/IP video inputs
- Max 6/12 channels IP camera inputs, each channel up to 5MP; Max 20/40Mbps Incoming Bandwidth
- Long transmission distance over coax cable
- Supports 1 SATA HDD, up to 6TB



CAMERA FEATURES:

- Max. 20fps@5MP
- HD and SD output switchable
- 2.8mm fixed lens
- Max. IR length 20m, Smart IR
- IP67, DC12V

EXP-4CHN-2BUL-5MP-1

4CHN 2CAM 5MP Bullet



- Max. 20fps@5MP
- HD and SD output switchable
- 2.8mm fixed lens
- Max. IR length 20m, Smart IR
- IP67, DC12V



System Overview

Experience 5MP video and the simplicity of using existing cabling infrastructure with HDCVI. The 5MP HDCVI camera features a compact design and offers a high quality image at a friendly price. It offers various vari-focal/fixed lens models with a multi-language OSD and HD/SD switchable output. Its structural flexibility and high cost-performance makes the camera an ideal choice for SMB solutions.

Functions

4 Signals over 1 Coaxial Cable

HDCVI technology supports 4 signals to be transmitted over 1 coaxial cable simultaneously, i.e. video, audio*, data and power. Dual-way data transmission allows the HDCVI camera to interact with the HCVR, such as sending control signal or triggering alarm. Moreover, HDCVI technology supports PoC for construction flexibility.

* Audio input is available for some models of HDCVI cameras.

Long Distance Transmission

HDCVI technology guarantees real-time transmission at long distance without any loss. It supports up to 700m for 5MP HD video via coaxial cable, and up to 300m via UTP cable.*

Simplicity

HDCVI technology inherits the born feature of simplicity from traditional analog surveillance system, making itself a best choice for investment protection. HDCVI system can seamlessly upgrade the traditional ana-log system without replacing existing coaxial cabling. The plug and play approach enables full HD video surveillance without the hassle of configuring a network.

Smart IR

The camera is designed with microcrystalline LED IR illumination for best lowlight performance. Smart IR is a technology to ensure brightness uniformity in B/W image under low illumination. The unique Smart IR adjusts to the intensity of camera's infrared LEDs to compensate for the distance of an object, and prevents IR LEDs from overexposing images as the object come closer to the camera.

Multi-formats

The camera supports multiple video formats including HDCVI, CVBS and other two common HD analog formats in the market. The four formats can be switched over through OSD menu or by PFM820(UTC controller). This feature makes the camera to be compatible with not only XVRs but also most end users' existing HD/SD DVRs.

Multi-language OSD

OSD menu provides multiple image adjustments and function settings to meet the requirements of different monitoring scenes. The OSD menu includes configurations such as backlight mode, day/night, white balance, privacy mask and motion detect. The camera supports 11 languages for OSD menu, namely, Chinese, English, French, German, Spanish, Portuguese, Italian, Japanese, Korean, Russian and Polish.

Protection

The camera's outstanding reliability is unsurpassed due to its rugged design. The camera is protected against water and dust with IP67 ranking, making it suitable for indoor or outdoor environments.

With working temperature range of -40°C to +60°C (-40°F to +140°F), the camera is designed for extreme temperature environments.

Supporting ±30% input voltage tolerance, this camera suits even the most unstable power supply conditions. Its 4KV lightning rating provides protection against the camera and its structure from the effects of lightning.

EXP-4CHN-2BUL-5MP-1

Technical Specification

Camera

Image Sensor	1/2.7" CMOS
Effective Pixels	2592(H)×1944(V), 5MP
Scanning System	Progressive
Electronic Shutter Speed	PAL: 1/25~1/100000s NTSC: 1/30~1/100000s
Minimum Illumination	0.04Lux/F2.0,, 30IRE, 0Lux IR on
S/N Ratio	More than 65dB
IR Distance	Up to 20m (66feet)
IR On/Off Control	Auto / Manual

Lens

Lens Type	Fixed lens / Fixed iris
Mount Type	Board-in
Focal Length	2.8mm
Max Aperture	F1.85
Angle of View	H: 77.5° (93°, 49°) v: 56.5° (68°, 37°)
Focus Control	N/A
Close Focus Distance	11400mm (800mm, 2500mm) 55.12" (31.50", 98.43")

DORI Distance

Note: The DORI distance is a "general proximity" of distance which makes it easy to pinpoint the right camera for your needs. The DORI distance is calculated based on sensor specification and lab test result according to EN 62676-4 which defines the criteria for Detect, Observe, Recognize and Identify respectively.

	DORI Definition	Distance
Detect	25px/m (8px/ft)	2.8mm:63m(207ft) 3.6mm: 80m(262ft) 6mm: 120m(394ft)
Observe	63px/m (19px/ft)	2.8mm:25m(83ft) 3.6mm: 32m(105ft) 6mm: 48m(157ft)
Recognize	125px/m (38px/ft)	2.8mm:13m(41ft) 3.6mm: 16m(52ft) 6mm: 24m(79ft)
Identify	250ppm (76px/ft)	2.8mm: 6m(21ft) 3.6mm: 8m(26ft) 6mm: 12m(39ft)

Pan / Tilt / Rotation

Pan/Tilt/Rotation	Pan: 0° ~ 360° Tilt: 0° ~ 90° Rotation: 0° ~ 360°
-------------------	---

Video

Resolution	5MP (2592×1944)
Frame Rate	20fps@5MP, 25/30fps@4MP, 25/30@1080P
Video Output	1-channel BNC high definition video output / CVBS video output (Can switch)
Day/Night	Auto (ICR) / Manual

OSD Menu	Multi-language
BLC Mode	BLC / HLC / DWDR
WDR	DWDR
Gain Control	AGC
Noise Reduction	2D
White Balance	Auto / Manual
Smart IR	Auto / Manual

Certifications

Certifications	CE (EN55032, EN55024, EN50130-4) FCC (CFR 47 FCC Part 15 subpartB, ANSI C63.4-2014)
----------------	--

Interface

Audio Interface	N/A
-----------------	-----

Electrical

Power Supply	12V DC ±30%
Power Consumption	Max. 3.9W (12V DC, IR on)


Environmental

Operating Conditions	-40°C ~ +60°C (-40°F ~ +140°F) / Less than 95% RH * Start up should be done at above -40°C (-40°F)
Storage Conditions	-40°C ~ +60°C (-40°F ~ +140°F) / Less than 95% RH
Ingress Protection & Vandal Resistance	IP67

Construction

Casing	Plastic
Dimensions	70mm×70mm×149mm (2.76"×2.76"×5.87")
Net Weight	0.15kg (0.33lb)
Gross Weight	0.19kg (0.42lb)

Dimensions (mm/inch)




EXP-4CHN-2BUL-5MP-1

4CHN 2CAM 5MP Bullet



- H.265+/H.265 dual-stream video compression
- Supports HDCVI/AHD/TVI/CVBS/IP video inputs
- Max 6/12 channels IP camera inputs, each channel up to 6MP;
- Max 24/48Mbps incoming bandwidth
- Long transmission distance over coax cable
- Supports 1 SATA HDD, up to 6TB
- Smart Search and Intelligent Video System



System Overview

Designed as a full compatibility product, this unit is able to provide end user the simplicity of analog system, namely lower system cost, simple installation and use of existing cable. And with the adoption of Smart H.265+/H.265, the series improves encoding efficiency, saving on bandwidth/storage costs. It is ideal for a wide range of civil applications such as retail store, home protection and so on.

Functions

Smart H.265+

Smart Codec, H.265+ can reduce up to 90% bit rate and storage requirements compared with H.264 without having to invest in new cameras.

HDCVI/AHD/TVI/CVBS/IP Auto-detect

The unit can auto recognize the signal of front-camera without any setting. It makes operation more friendly and convenient.

High Definition Camera Input

The unit supports up to 5MP HDCVI camera and 6MP IP camera input.

Coaxial Audio/Upgrade/Alarm

The integrated design can reduce wiring troubles which makes it much more cost-effective and convenient for installation.

Long Distance Transmission

The HDCVI system supports long distance transmission over coaxial cable and UTP, max. 700m for 4K/4MP, 800m for 1080P and 1200m for 720P.

Intelligent Video System (IVS)

With built-in intelligent video analytics, the unit has the ability to detect and analyze moving objects for improved video surveillance. The unit provides optional standard intelligence at the edge allowing detection of multiple object behaviors such as abandoned or missing objects. IVS also supports Tripwire analytics, allowing the camera to detect when a pre-determined line has been crossed.

Face Detection

It is a typical technology being used in a variety of applications for searching or identification of individuals.

Smart Search

This function helps you get more motion detect video during a short time through drawing a region when playback. It is very useful when an emergency occurs.

EXP-4CHN-2BUL-5MP-1

Technical Specification

System

Main Processor Embedded Processor

Operating System Embedded LINUX

Video and Audio

Analog Camera Input 4/8 Channel, BNC

HDCVI Camera 5MP, 4MP, 1080P@25/30fps, 720P@50/60fps, 720P@25/30fps

AHD Camera 5MP, 4MP, 1080P@25/30, 720P@25/30fps

TVI Camera 5MP, 4MP, 1080P@25/30, 720P@25/30fps

CVBS Camera PAL/NTSC

IP Camera Input 4+2/8+4CH, each channel up to 6MP

Audio In/Out 1/1, RCA

Two-way Talk Reuse audio in/out, RCA

Recording

Video Compression H.265+/H.265/H.264+/H.264

Resolution 5M-N, 4M-N, 1080P, 1080N, 720P, 960H, D1, CIF

Record Rate
Main Stream:
4CH: the 1st channel 5M-N(1~10fps);
8CH: the 1st & 2nd channels 5M-N(1~10fps);
other channels 4M-N/1080P(1~15fps); 1080N/720P/960H/
D1/CIF (1~25/30fps)
Sub stream:
CIF/QCIF (1~15fps)

Video Bit Rate 32Kbps ~ 6144Kbps Per Channel

Record Mode Manual, Schedule (General, Continuous), MD (Video detection: Motion Detection, Video Loss, Tampering), Alarm, Stop

Record Interval 1 ~ 60 min (default: 60 min), Pre-record: 1 ~ 30 sec, Post-record: 10 ~ 300 sec

Audio Compression AAC(only for the 1st channel), G.711A, G.711U, PCM

Audio Sample Rate 8KHz, 16 bit Per Channel

Audio Bit Rate 64Kbps Per Channel

Display

Interface 1 HDMI ,1 VGA

Resolution 1920×1080, 1280×1024, 1280×720

Multi-screen Display
When IP extension mode not enabled:
4CH: 1/4
8CH: 1/4/8/9
When IP extension mode enabled:
4CH: 1/4/6
8CH: 1/4/8/9/16

OSD Camera title, Time, Video loss, Camera lock, Motion detection, Recording

Network

Interface 1 RJ-45 Port (100M)

Network Function HTTP, HTTPS, TCP/IP, IPv4/IPv6, UPnP, RTSP, UDP, SMTP, NTP, DHCP, DNS, IP Filter ,DDNS, FTP, Alarm Server, P2P,IP Search (Supports Dahua IP camera, DVR, NVS, etc.)

Max. User Access 128 users

Smart Phone iPhone, iPad, Android

Interoperability ONVIF 16.12, CGI Conformant

Video Detection and Alarm

Trigger Events Recording, PTZ, Tour, Video Push, Email, FTP, Snapshot, Buzzer and Screen Tips

Video Detection Motion Detection, MD Zones: 396 (22 × 18), Video Loss, Tampering and Diagnosis

Alarm input N/A

Relay Output N/A

Playback and Backup

Playback 4CH: 1/4
8CH: 1/4/8

Search Mode Time /Date, Alarm, MD and Exact Search (accurate to second)

Playback Function Play, Pause, Stop, Rewind, Fast play, Slow Play, Next File, Previous File, Next Camera, Previous Camera, Full Screen, Repeat, Shuffle, Backup Selection, Digital Zoom

Backup Mode USB Device/Network

Storage

Internal HDD 1 SATA Port, up to 6TB capacity

eSATA N/A

Auxiliary Interface

USB 2 USB 2.0

RS232 N/A

RS485 N/A

Electrical

Power Supply DC12V/1.5A

Power Consumption (Without HDD) <10W

Construction

Dimensions Cooper 1U, 197mm×192mm×41mm (7.8"×7.6"×1.6")

Net Weight (without HDD) 0.54kg (1.19lb)

Gross Weight 1kg (2.2lb)

Installation Desktop installation

Environmental

Operating Conditions -10°C ~ +45°C (+14°F ~ +113°F), 10~ 90% RH

Storage Conditions -20°C ~ +70°C (-4°F ~ +158°F) , 0~ 90% RH

Third-party Support

Third-party Support Dahua, Arecont Vision, AXIS, Bosch, Brickcom, Canon, CP Plus, Dynacolor, Honeywell, Panasonic, Pelco, Samsung, Sanyo, Sony, Videotec, Vivotek, and more

Certifications




FCC: Part 15 Subpart B

Certifications CE: CE-LVD: EN 60950-1/IEC 60950-1
CE-EMC: EN 61000-3-2, EN 61000-3-3, EN 55032, EN 50130, EN 55024

UL: UL 60950-1

EXP-4CHN-2BUL-5MP-1

Dimensions (mm)



Rear Panel

- | | |
|----------------------------|---------------------|
| 1 VIDEO IN | 5 HDMI Interface |
| 2 AUDIO IN, RCA Connector | 6 USB Interface |
| 3 AUDIO OUT, RCA Connector | 7 Network Interface |
| 4 VGA Interface | 8 DC12V Power Input |