

Advantages

Minimum size at high output

Inherently short-circuit proof

Dual input voltage for series or parallel connection

Also with dual output voltage for series or parallel connection

Designed for high ambient temperatures

Permanent corrosion protection, high insulation value and maximum electrical reliability thanks to XtraDenseFill resin encapsulation


Self-extinguishing potting and hood material

Applications

As a mains transformer for adjustment of the voltage and simple electrical isolation.

As a safety transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

Sample application



Standards

Safety isolating transformer to: VDE 0570 Part 2-6, DIN EN 61558-2-6, EN 61558-2-6, IEC 61558-2-6, UL 5085-1/-2, CSA 22.2 No.66

Approvals

UL 5085-1/-2, CSA 22.2 No.66







Safety isolating transformer **AVB 1,0/2/6**

Type	AVB 1,0/2/6	Type
Input		Terminal and mounting
Rated input voltage	2 x 115 Vac	Terminals
Rated frequency	50 - 60 Hz	Pin (ø)
Output Rated output voltage Rated Power No-load voltage (app. x factor) No-load loss (typ.) Efficiency		Measures and weights Core type
Rated output voltage	2 x 6 Vac	Core type
Rated Power	1 VA	₹ Weight
No-load voltage (app. x factor)	1.32	·SE
No-load loss (typ.)	0.90 W	Tage 1
Efficiency	55.0 %	
Standards		Weight Weight
Classification	Safety isolating transformer	
Approvals		20.0 10.0 PRI
Approvals	cURus	<u> </u>
Environment		<u> </u>
Ambient temperature max.	70 °C	
Safety and protection		l -
Туре	Encapsulated	
Insulation class	VDE=B, UL=class 105	
Protection index	IP 00	
Safety class (prepared)	II	
Short circuit strength	inherently short-circuit proof	
Order numbers		
Order Number	AVB 1,0/2/6	

