




Knapsack Sprayer - 10 litres

Knapsack Sprayer with a 10 litres tank, more comfortable, lighter, compact and ergonomic. Ideal for pesticides application in general, fertilizers and organic products. Indicated for gardening, gardens, orchards and house disinfection.





Pest contro



Application in gardens



Application in vegetable gardens



- Compact machine, ergonomical, easy to use and to maintain.
- A wide range of optional accessories for all types of applications optimize cost-benefit.
- Ideal for the application of chemicals and organic products in small vegetable gardens, orchards and pest control.
- Locking device

 Discharge valve with a locking device that avoids incidental

spraying.

• A more resistant pump and a pressure relief valve that provides more durability to the sprayer.

- **5** Double system of internal agitation: mechanical by an agitator and hydraulic by liquid recirculation (by-pass).
- 6 Discharge set with new Super 5 valve, with an exclusive locking device (open/closed) to avoid incidental spraying. Curved lance and universal nozzle with adjustable tip.
- 7 Chassis with brakets resistant to impact and one piece pumping shaft.
- 8 Relief valve incorporated in the cylinder, avoids excessive pressure providing more durability to the equipment.
- **9** Padded carrying straps, water proof with self-regulating buckles.
- 10 **New Filter:** large filter to make the filtration process quicker and progressive filtration in four stages, with filter in the tank, in the pump, in the valve handle and in the nozzle. Does not block.

A service kit with most replaceable spare parts and nozzle for herbicide application.

technical specifications

	Code 428.00/428.01
Tank capacity	
Net weight	3,2Kg (7,0 pound)
Pump polyethylene / polypropylene	Piston Type
Working pressure (maximum)	300kPa - (45 psi)
Flow rate of the adjustable tip	600ml/min (0,15 gal/min)
Packaging	407 x 172 x 485mm (16" x 6,8" x 19")

Guarany's Mission - to offer the best quality products, with innovative features that can be of public use, use well as the best services, always respecting the environment, people and markets, besides guaranteeing the satisfaction of our customers and employees.



tradition and technology

www.guaranyind.com.br

rod. waldomiro correa de camargo, km 56,5 cep 13308-200 itu sp brasil **(55 11) 2118 8400**

Distributor

(1) Zicard September/2010 version: 01 1542.04.00 Guarany reserves the right to change specifications without prior

brackets are in USA system.

values between

whenever