




**DFROBOT**<sup>®</sup>  
DRIVE THE FUTURE

# 7" Capacitive Touch Panel Overlay for LattePanda V1 IPS Display

SKU:FIT0478



## INTRODUCTION

This is a capacitive touch panel overlay for your [LattePanda V1 single board computer](#) (**not compatible with LattePanda Alpha & Delta**). Overlay the adhesive panel on your [LattePanda 7" display](#) (not included), connect the FPC connector and power the board. This gives you a high-quality user interface for your project!

**Note:** We have recently released a new batch of touch panels that have a higher sensitivity. Drivers on boards manufactured after May 2016 will include the drivers pre-installed on the system.

If you have purchased an older version LattePanda but want to use the newer capacitive touch panel, you can download the V1.1 drivers below and manually install them.

PLEASE NOTE: "install.bat" must be run as an administrator to update the driver correctly.  
**NOT compatible with LattePanda Alpha and Delta edition**

### What is [LattePanda](#)?

A [LattePanda](#) is a complete [Windows 10 single-board computer](#)! It includes everything a regular PC has and can do anything that a regular PC does. It is compatible with almost every gadget you know: printers, joysticks, cameras, and more. Any peripherals that work on your PC will work on a LattePanda. A [LattePanda](#) comes pre-installed with a full, pre-activated version of Windows 10, where you can install powerful tools such as Visual Studio, NodeJS,



**DFROBOT**<sup>®</sup>  
DRIVE THE FUTURE

Java, Processing, and more. Using existing APIs, you can develop your own software and hardware projects on a LattePanda as you would on a normal PC - C#, Javascript, Ruby, and so on. Say goodbye to your bulky laptop!

## ***SPECIFICATION***

- Capacitive Touch Control
- Transmittance : 85%
- Surface Hardness : 6H
- Response Time:  $\leq 16$ ms
- Tapping Durability: 200,000,000 times
- Supports LattePanda V1 (not compatible with LattePanda Alpha & Delta)
- 10cm FPC Extension Cable
- Dimensions: 164.0mm x 96.0mm