GNC 24-15



Advantages

Unsusceptible to voltage surges or transients

High overload capacity

DC OK signalling via LEDs

Capacitor switching at the output

Very good corrosion protection and low noise thanks to vacuum

Impulse loading MKT-capacitors

Varistor wiring


Contact protected screw connection terminals complying with UVV BGV A3

GNC 24-2,5 with combination footplate for bolted and rail mounting

Applications

Robust DC power supply for harsh industrial applications.

Sample application



Standards

Non-stabilised dc power supply / Safety isolating transformer to VDE 0570 part 2-6, EN 61558-2-6, IEC 61558-2-6, UL 1012

Approvals





UL 5085-1/-2, CSA 22.2 No.66





Single-phase, non stabilized DC power supply **GNC 24-15**

	Type	GNC 24-15		Туре	GNC 24-15
Ĵ٢	Input		30	Terminal and mounting	
i+	Input rated voltage	230/400 Vac, ±15 Vac	(,)	Terminals	Screw-type terminals
	Rated frequency	50 - 60 Hz		Fixing method	Base plate
data	Output		data	Fixing screws	M6
Electrical da	Output rated voltage	24 Vdc		Measures and weights	
	Power	360.00 W	ō	Weight	8.30 kg
	Output rated current	15.00 A	.은		
G	Ripple factor	3 %	la la		55.0 94.0
읦	Approvals		Mechanical	✓ 160.0 →	55.0 94.0
	Approvals	cURus (transformer only)	Ž	160.0	
	Environment				
	Ambient temperature max.	60 °C			
	Type of cooling	self-cooling			
	Safety and protection			•	1 E
	Туре	Open type		200.0	
	Insulation class	VDE=B, UL=class 130			
	Protection index	IP 00			
	Safety class (prepared)	1			
	Short circuit strength	non-short-circuit proof			
	Order numbers			<u> </u>	
	Order Number	GNC 24-15		122.0 →	-
				150.0	
				100.0	112.0 90.0

