



Item #: **EVNSL0508A-1000**  
CAT5e 350-MHz Solid Ethernet Bulk Cable  
- Shielded (F/UTP), CMR PVC, 1000-ft.  
(304.8-m) Spool

HDBaseT™ Recommended CAT5e cable.

## PRODUCT FEATURES

---

- Ideal for long runs in industrial environments.
- Meets TIA/EIA-568-C CAT5e specifications.
- Low attenuation and near-end crosstalk provide excellent transmission.
- Features aluminum Mylar; tape. Foil shield protects against noise and EMI/RFI interference.
- Guaranteed for life
- 

### Details:

- Ideal for long runs in industrial environments. Meets TIA/EIA-568C CAT5e specifications. Low attenuation and near-end crosstalk provide excellent transmission. Features aluminum Mylar tape. Foil shield protects against noise and EMI/RFI interference.

<b>General</b>	
ACR (100 m/dB Min.)	100 MHz: 13.3
Attenuation (100 m/dB Min.)	100 MHz: 22.0; 200 MHz: 32.4; 300 MHz: 36.0; 350 MHz: 44.9
ELFEXT (dB Min.)	100 MHz: 23.8; 200 MHz: 17.7; 300 MHz: 14.2; 350 MHz: 12.9
NEXT (dB Min.)	100 MHz: 35.3; 200 MHz: 30.8; 300 MHz: 28.2; 350 MHz: 27.1
PS-ACR	100 MHz: 10.3

PS-ELFEXT	100 MHz: 20.8; 200 MHz: 14.7; 300 MHz: 11.2; 350 MHz: 9.9
PS-NEXT	100 MHz: 32.3; 200 MHz: 27.8; 300 MHz: 25.2; 350 MHz: 24.1