




DFROBOT[®]
DRIVE THE FUTURE

Gravity: Analog Gas Sensor (MQ2) For Arduino

SKU:SEN0127



INTRODUCTION

This is a generic Arduino gas sensor. It has MQ2 probe which is able to detect LPG, i-butane, propane, methane ,alcohol, Hydrogen, smoke.

It can be used in gas leakage detecting device in consumer and industry markets. It has a high sensitivity and fast response time.

The sensitivity can be adjusted by the potentiometer. The output is proportional to the density of gas. You can use analog reading to read the data from this sensor.

To ease the difficulty of using this sensor, a [Gravity](#) Interface is adapted to allow plug&play. The [Arduino IO expansion shield](#) is the best match for this sensor connecting to your [Arduino](#). As this sensor can work at 3.3V which makes it compatible with [Raspberry Pi](#), [intel edison](#), joule and curie.

Improvement List

- Standard assembling structure (Times-of-5mm Center distance between two 3mm mounting holes)
- Easily recognitive interfaces of sensors ("A" for analog and "D" for digital)



DFROBOT[®]
DRIVE THE FUTURE

- Icons to simply illustrate sensor function
- High quality connector
- Immersion gold surface

SPECIFICATION

- Power supply needs: 5V
- Interface type: Analog
- Wide detecting scope
- Fast response and High sensitivity
- Simple drive circuit
- Stable and long life
- Size:36.4x26.6mm (1.4x1")