


TECHNICAL DATA SHEET

PRO-ELEC

RoHS
Compliant

METAL DETECTABLE CABLE TIES

MODELS: PELB1112- PELB1118



Standards:

UL Flammability for raw materials: 94V2

Application:

Made from detectable Nylon (PA66) compounds. These products are intended for use in the proximity of food processing, handling, and packaging operations. In addition, these products are used for cable management on food processing and packaging equipment, and inside electrical control panels found in food processing and packaging operations.

Colour	Size (LxW)	Max. Bundle Ø	Tensile Strength	Pack Quantity	Model
Blue	100x2.50mm	20.50mm	80N	100	PELB1112
	150x3.60mm	36.00mm	180N		PELB1113
	200x3.60mm	52.50mm	180N		PELB1114
	200x4.80mm	49.50mm	230N		PELB1115
	300x4.80mm	81.00mm	230N		PELB1116
	370x4.80mm	103.50mm	230N		PELB1117
	370x7.60mm	102.00mm	540N		PELB1118

Important Notice: This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.

PRO-ELEC