



OSK9-2TCER

► OCCUPANCY SOLUTION KIT



Occupancy Solution Kit
 2 DOOR TOTAL COUNT
 DXM1200 900 MHz 1W Controller
 PSW-24-1 Power Supply
 (2) DX80 Directional Pairs
 (2) Hardware Packets
 (2) TL70DXN9GRQ-INOUTIKIT
 DIRECT SELECT Node
 Part Number: 810362

SPECIFICATIONS

Sensor Mode	Emitter-Receiver
Occupancy Monitoring Application	Total Count
Monitored Doors	2
Feature: Hazardous Area	No
EtherNet/IP	Yes
Modbus RTU	Yes
Modbus/TCP	Yes
RS-232	No
RS-485	Yes
Wireless	Yes
Wireless Radio Frequency	900 MHz

Max Op. Temperature (°C)	50
Voltage	10-30 V dc
Power Supply	24 V dc 1.0 Amp
Star Topology	Yes
Tree Topology	No
Ships With Battery	Yes
Point-to-Multipoint Topology	Yes
Point-to-Point Topology	Yes
Relative Humidity	90% at 50° C
Battery Type/Size	Lithium/C and D

COMPATIBLE PRODUCTS

	<p>PSW-24-1</p> <p>DC Power Supply - Wall Mount
Input: 100 -240 V ac 50/60 Hz: Multi-blade outlet plug
Output: 24 V dc 1A: 2 m (6.5 ft) Euro 4-pin Connector
UL Listed Class 2</p>
--	--

DXM 100 SERIES

	<p>DXM1200-B1R1</p> <p>DXM1200 Controller
IP67
DX80 ISM 900 MHZ Radio (PE5)
LCD Display</p>
--	---

DIRECT SELECT

	<p>DX80N9DSTS</p> <p>Wireless Operator Interface Node
900 MHz 1W, LCD Display 0-999
Multicolor Capacitive Touch</p>
--	--

	<p>BWA-HW-OSK-001</p> <p>Bracket DX80 Occupancy
1/2 NPT Black Delrin Jam Nut
Zing Plated Steel Washer</p>
	<p>TL70DXN9GRQ-INOUTIKIT</p> <p>TL70DXN9GRQ-INOUTIKIT</p>



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America