

1/4" INSTRUMENT CABLE

TBK SERIES OVERVIEW

To meet the sonic expectations of discerning musicians around the world, the TBK Series instrument cable contains OFC conductors and a layer of conductive PE insulation. The use of these materials ensures that the final product consistently delivers a solid performance. Conductive PE absorbs changes in capacitance that occur when musicians run, walk, or shake their instruments on stage.

The IO-T2MBK connectors feature an extremely durable nickel tin plated brass shell and includes both a metal clamp as well as a metal pressure chuck which tighten onto the cable to provide extended strain relief. The gold plated plug contacts, silver plated wire terminals, and XLPE insulation all ensure the best possible signal flow and extend the useful life of the cable.

The cable comes equipped with a durable and flexible PVC jacket to protect the cable from whatever life throws at it. Additionally, a copper spiral shield protects the conductors from EMI. The result? A dependable companion for any musician.







SPECIFICATIONS

Product

Part Number: IO-IC109XXX-T2MBK

Number of Conductors: 1 plus shield

Conductors

Details: 50/0.12mm BC OFC

Size: 20 AWG

Electrical and Mechanical

Characteristics

Conductor DC Resistance: $0.035 \pm 1\% \Omega/m$

Shield DC Resistance: $0.033 \pm 1\% \Omega/m$

Capacitance Between Conductor and Shield: ≤ 33.3 pF/ft

Voltage Breakdown: 500 V

Flex Life: ≥ 17,700

Tensile Strength: ≥ 197.82 N

Applicable Temperature: -20°C ~ +60° C (-4°F ~ +140°F)

Peak Temperature: -40° C $\sim +70^{\circ}$ C $(-40^{\circ}$ F $\sim +158^{\circ}$ F)

Insulation

Material: Conductive PE

Shield

Details: Spiraled

Construction: 55/0.12 BC OFC

Jacket

O.D.: **6.0mm**

Material: **PVC**

Color: Black

DRAWING



STANDARDS & CLASSIFICATIONS

