

Tab M10 FHD Plus (2nd Gen) ZA6H0018GB

Lenovo

PSREF
Product Specifications
Reference

PERFORMANCE

Processor

MediaTek Helio P22T (8C, 8x A53 @2.3GHz)

Graphics

Integrated IMG PowerVR GE8320 GPU

Chipset

MediaTek SoC Platform

Memory

4GB Soldered LPDDR4x-3200

Storage

128GB eMMC

Expandable Memory

MicroSD card (Up to 256GB)

Card Reader

MicroSD Card Slot

Storage Support

- 128GB eMMC on systemboard
- MicroSD card, supports FAT32 up to 256GB, exFAT up to 1TB

Camera

Front 5.0MP / Rear 8.0MP

Microphone

2x, Array

Speakers

Dual side speaker, tuned with Dolby® Atmos®

Sensors

- Ambient light sensor (ALS)
- Hall sensor
- Accelerometer (G) sensor
- Proximity sensor

Vibrator

Vibrator

Battery

Integrated 5000mAh

Max Battery Life

Standby Time: Over 6 weeks
Online Video Playback Time: 8.5 hr
Browsing Time: 9 hr

Charging Time

Over 3.5 hours

Power Adapter

5V / 2.0A

DESIGN

Display

10.3" FHD (1920x1200) TDDI 330nits

Touchscreen

10-point Multi-touch

Case Material

Metal

Pen

None

Dimensions (WxDxH)

244.2 x 153.3 x 8.15 mm (9.61 x 6.03 x 0.32 inches)

Weight

460 g (1.01 lbs)

Case Color

Iron Grey

SOFTWARE

Operating System

Android Pie

Preinstalled Software

- Tips
- Lenovo® Vantage
- Netflix
- Google Photos
- Google Play
- Kids Mode
- Google
- Google Chrome
- Dolby Atmos

CONNECTIVITY

WLAN + Bluetooth™

11a/b/g/n/ac, 1x1 + BT5.0

WWAN

None

Location

GPS + GLONASS

SIM Card

Not configured

VoiceCall

No

Standard Ports

- 1x USB-C 2.0 (support data transfer, OTG and Power Delivery)
- 1x headphone / microphone combo jack (3.5mm)
- 1x Pogo pin connector (2-point)

Optional Ports

1x microSD card slot (WiFi model)

SERVICE

Base Warranty

1-year, Depot

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- RoHS

Other Certifications

TÜV Rheinland Low Blue Light certified

MODEL

TopSeller : Yes

Announce Date : 2020-08-11

EAN / UPC / JAN : 195042079883



The product image is a sample, it may not match the real color of this model
For a full list of this model's configurations and device specifications, please visit: <https://psref.Lenovo.com>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Technician Installed Customer
- Onsite Support
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference