

## C4AQBW5300M3NJ

C4AQ M, Film, Metallized Polypropylene, Automotive DC Link, 30 uF, 5%, 1100 VDC, 85°C, Lead Spacing = 52.5mm



Click [here](#) for the 3D model.

### Dimensions

L	57.5mm +0.8/-0.7mm
H	50mm +0.3/-0.7mm
T	35mm +0.5/-0.7mm
S	52.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm +0/-2mm
F	1.2mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	23

### General Information

Series	C4AQ M
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	4 Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Miscellaneous	Rth = 10 C/W.

### Specifications

Capacitance	30 uF
Capacitance Tolerance	5%
Voltage DC	1100 VDC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.02% (10 kHz 25C)
Insulation Resistance	1 MOhms
Max dV/dt	20 V/us
Resistance	4.8 mOhms (10kHz 70C)
Ripple Current	23 Amps Irms (10kHz 70C), 600 Amps Ipk
Inductance	15 nH