



Date revision	symbol	Kai	Revised	Record	Thing	Revised No.	Design	Review	Approval
2015. 5.27		New number				GK2013-000-50	Kobayashi Ito		



■ Finish

1. 1. Male  
Electric pressure resistance: AC900V, 1 minute  
Insulation resistance: DC500V, 1000MΩ or more  
Contact resistance: 1A or less, 8mΩ or less
2. 2. Samadhi Case  
Den Pressure: AC300V (DC420V)  
Den Flow: 2A
3. 3. Wire connection hole diameter: φ1.0 mm
4. Wire connection method: Soldering
5. table Show: PRC05 ... TMW
6. Compatible cable finished outer diameter range

Soldering side Seen more  
Contact symbol (3/1)



Code ⑩ Sleeve	cable	Compatible cable
	Introductory port size	Finished outer diameter range
At the time of application	φ4.0	φ2.8-φ3.8
When not applied	φ5.2	φ4.0-φ5.0

Note

The ▽ mark in the figure indicates the connector guide position.

12	Special set screw with slip	Steel	Nickel plating 1	
11	sleeve	Vinyl chloride-1		Attachments
Ten	Phillips pan head machine screw	Brass	Nickel plating 2	
9	Rear shell	Brass	Nickel plating 1	
8 #	22 S pin contact	Brass	Nickel base gold plating 3	
7	Ferrule	Brass	Nickel plating 1	
6 M	type rear insulator	PPS resin-1		
5 M	type front insulator	PPS resin-1		
Four	spring	Steel	Nickel plating 1	
Four	gasket	Silicon rubber-1		
2	Slide ring	Brass	Nickel plating 1	
1	Insert shell	Brass	Nickel plating 1	

Reference diagram  
'18 .11.22  
Engineering Department

2015. 5.27	G K2 013-000-50	No.	Design and technical inspection	Approval name	<b>EPRC05-P3M</b>		
From date	line Record Thing	three					
1	2/1 mm	Horn			Figure number		
Edition	Shaku Degree Rank	Law	2015: 5:27	2015: 5:27	2015: 6:11	2015: 6:17	EPRC05-1004 1
Tajimi Electrics Co., Ltd.							