

Quam DTS4

The DTS4 is a desktop intercom station consisting of a 3", 8 Ohm, square frame loudspeaker with a 2.35 oz. ceramic magnet, and a moisture resistant cone, a push-to-talk (PTT) button, and a 3-pin XLR microphone connector. The DTS4 has a protective steel screen mounted between the loudspeaker and the enclosure perforations. It is equipped with tamper resistant, #6-32 x 1", 'pin-in-torx', stainless steel screws. The DTS4 has a durable, charcoal gray, powder coat finish.



APPLICATION	Intended Use: Program Material:	Indoor environment Signal tones and voice
AUDIO PERFORMANCE	Average Sensitivity: Station Power Rating: Magnet Type & Weight: Frequency Response: Nominal Coverage Angle: Loudspeaker Connection: Microphone Connection:	87dB SPL, 1W/1M 4W RMS, EIA 426A Standard BeFe Ceramic, 2.35 oz. Nominal 300Hz - 10kHz, EIA 426A Standard 90° Included Angle, -6dB/2kHz, Half Space 7" Color-coded, Pre-tinned Leads 3-pin XLR (solder cups)
COMPONENT	Dimensions: Weight: Loudspeaker Model: Loudspeaker Specs: Enclosure: Grille: Switch: Finish:	5 1/2" (H) x 6 7/8" (W) x 4 1/4" (D) 2.75 lbs. 30C25Z8OT 3" O.D. loudspeaker, 2.35 oz. magnet, moisture resistant cone Heavy gauge, stamped steel with knockout for 1/2" conduit & keystone jack Standard perforated steel with protective screen Pushbutton, normally open, rated at 48VDC, 2A max., screw terminals Charcoal gray, powder coat finish

