

MCE 494

Condenser Microphone

Order # 465.577



FEATURES

- Cardioid polar pattern
- Direct powering
- Unobtrusive design
- High-quality voice reproduction
- Excellent noise rejection

APPLICATIONS

The MCE 494 is a condenser microphone intended for direct connection to notebooks, mobile DAT and MD recorders in teleconferencing, speech recognition and interviewing applications. The microphone is powered from the microphone input of the connected device. Due to its cardioid polar pattern, the MCE 494 has high-gain-before feedback (PC loudspeaker) and rejects background sounds such as drive noise. The wide frequency response gives clear and precise voice reproduction with high intelligibility.

OPTIONAL ACCESSORY

WS 20 sw Wind shield for MCE 494, black Order # 439.975

Germany

Theresienstr. 8
D-74072 Heilbronn
Tel. +49 (0)71 31 / 6 17-0
Fax +49 (0)71 31 / 617-224
E-mail: info@beyerdynamic.de
Internet: www.beyerdynamic.de

United States

56 Central Ave.
Farmingdale, NY 11735
Tel. +1 (631) 293-3200
Fax +1 (631) 293-3288
E-mail: salesUSA@beyerdynamic.com
Internet: www.beyerdynamic.com

Great Britain



17 Albert Drive
Burgess Hill RH15 9TN
Tel. +44 (0)1444 / 258 258
Fax +44 (0)1444 / 258 444
E-mail: sales@beyerdynamic.co.uk
Internet: www.beyerdynamic.co.uk

TECHNICAL SPECIFICATIONS

Transducer type	Condenser (back electret)	
Operating principle	Pressure gradient	
Polar pattern	Cardioid	
Frequency response	30 - 18,000 Hz (close miking)	
Open circuit voltage	approx. 20 mV/Pa	
Nominal impedance	approx. 2 k Ω	
Load impedance	> 10 k Ω	
Max. SPL at f = 1 kHz, k = 1%, R = 1 k	120 dB	
Signal-to-noise ratio at 1 Pa	60 dB	
A-weighted equivalent SPL	26 dB	
Connection	Mini stereo jack plug (3.5 mm) (L and R bridged)	
Dimensions	Length:	45 mm
	Diameter:	13.5 mm
Weight without cable	6.5 g	

FREQUENCY RESPONSE & POLAR PATTERN

This frequency response curve (measuring tolerance ± 2 dB) and polar pattern correspond to a typical production sample for this microphone.



WIRING DIAGRAM

