



H K Wentworth Group
Distributed and Supported in
the UK



hakko.com - hakko.co.uk

Packing List



FA400 Unit With British Plug + Instructions



A1001 Filter



FA400-15

Specifications:



FA400

Power consumption	18W (230V)
Noise level	60Hz : 51dB
Maximum suction capacity	Vertically : 1.0m ³ /min. (50Hz) / 1.1m ³ /min. (60Hz) Horizontally : 0.4m ³ /min. (50Hz) / 0.5m ³ /min. (60Hz)
Air velocity	Vertically : 1.0 m/sec. (50Hz) / 1.1 m/sec. (60Hz) Horizontally : 2.6 m/sec. (50Hz) / 2.9 m/sec. (60Hz)
Filter size	130(W) × 130(H) × 10(D)mm
Dimensions	166(W) × 212(H) × 113(D)mm
Weight	0.91 kg

* Weight (w/o cord)

* Noise level is measured at a distance of 1m from the face of unit.

* Maximum suction capacity is measured with a filter present.



- Vertically mounted:



Can absorb widespread smoke.



- Horizontally mounted:




Powerful absorption at closer area with high flow rate. Because of low height, it gives less shade keeping your working area light.

- Using a stand:



When sufficient space cannot be found or to absorb smoke from upper areas:



Recommended Extras:

(Available to purchase separately)

C1568

Arm Stand



A1001

Replacement Filters



H K Wentworth Group
Distributed and Supported in
the UK