

har-flex ang. hyb M 8P+36S SMT PL1 400pc



Part number	15 75 836 2601 000
Specification	har-flex ang. hyb M 8P+36S SMT PL1 400pc
HARTING eCatalogue	https://b2b.harting.com/15758362601000

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	har-flex [®]
Identification	Hybrid
Element	Male connector
Description of the contact	Angled

Version

Termination method	Reflow soldering termination (SMT)
Connection type	Motherboard to daughtercard Extender card
Number of contacts	44
Number of signal contacts	36
Number of power contacts	8
Performance level	1
Pack contents	400 pieces on reel

Technical characteristics

Contact spacing (mating side)	1.27 mm 2.54 mm
Rated voltage	acc. to IEC 60664-1
Rated voltage	50 V AC 120 V DC
Rated impulse voltage	1.5 kV
Pollution degree	2



Technical characteristics

Clearance distance	≥0.4 mm Signal contacts ≥1.74 mm Power contacts ≥1.11 mm Signal to power contacts
Creepage distance	≥0.4 mm PCB: Signal contacts ≥1.74 mm PCB: Power contacts ≥1.11 mm PCB: Signal to power contacts ≥0.4 mm Connector: Signal contacts ≥1.89 mm Connector: Power contacts ≥1.99 mm Connector: Signal to power contacts
Insulation resistance	>10 ¹⁰ Ω
Contact resistance	≤25 mΩ
Limiting temperature	-55 +125 °C
Mating cycles	≥500
Test voltage U _{r.m.s.}	0.5 kV Signal 1.39 kV Signal / Power 1.39 kV Power / Power
Isolation group	IIIa (175 ≤ CTI < 400)
Moisture Sensitivity Level (MSL)	1 acc. to ECA/IPC/JEDEC J-STD-020D
Process Sensitivity Level (PSL)	R0 acc. to ECA/IPC/JEDEC J-STD-020D
Coplanarity of contacts	0.12 mm

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Au over Pd/Ni Mating side Tin plated Termination side
Material flammability class acc. to UL 94	V-0

Commercial data


Packaging size	1
Country of origin	China
European customs tariff number	85366990
eCl@ss	27460201 PCB connector (board connector)



Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques acc. to IEC 60512-5-2



Derating curve 80%