



Foam Alcohol Hand Rub

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Issue date: 3/24/2017 Revision date: 7/8/2020

Version: 1.3

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name : Foam Alcohol Hand Rub
Product code : RHG 4440
Type of product : Biocide
SKU # : 2146691 | 2146692 | 2146693 | 2146694 | 2146695

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Industrial/Professional use spec : For professional use only

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Newell Europe Sàrl
Chemin de Blandonnet 8
CH-1214 Vernier - Switzerland
T +44(0)870 5686824
SDS.RCP@newellco.com

1.4. Emergency telephone number

Emergency number : +44(0)870 5686824

Country	Organisation/Company	Address	Emergency number	Comment
Ireland	National Poisons Information Centre Beaumont Hospital	PO Box 1297 Beaumont Road 9 Dublin	+353 1 809 2566 (Healthcare professionals-24/7) +353 1 809 2166 (public, 8am - 10pm, 7/7)	
United Kingdom	National Poisons Information Service (Belfast Centre) Royal Victoria Hospital	Grosvenor Road BT12 6BA Belfast	0344 892 0111	
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	
United Kingdom	National Poisons Information Service (Cardiff Centre) Gwenwyn Ward, Llandough Hospital	Penarth CF64 2XX Cardiff	0344 892 0111	
United Kingdom	National Poisons Information Service Edinburgh Royal Infirmary of Edinburgh	Little France Crescent EH16 4SA Edinburgh	0344 892 0111	
United Kingdom	Guy's & St Thomas' Poisons Unit Medical Toxicology Unit, Guy's & St Thomas' Hospital Trust	Avonley Road SE14 5ER London	+44 20 7188 7188	
United Kingdom	National Poisons Information Service (Newcastle Centre) Regional Drugs and Therapeutics Centre, Wolfson Unit	Claremont Place Newcastle-upon-Tyne NE1 4LP Newcastle	0344 892 0111	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Flammable liquids, Category 2 H225

Serious eye damage/eye irritation, Category 2 H319

Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

Foam Alcohol Hand Rub


Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)



Signal word (CLP) : Danger

Hazardous ingredients : Alcohol

Hazard statements (CLP) : H225 - Highly flammable liquid and vapour.
H319 - Causes serious eye irritation.

Precautionary statements (CLP) : P210 - Keep away from heat, sparks, open flames, hot surfaces. No smoking.
P233 - Keep container tightly closed.
P280 - Wear eye protection.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313 - If eye irritation persists: Get medical advice/attention.
P403+P235 - Store in a well-ventilated place. Keep cool.
P501 - Dispose of contents/container to an approved waste disposal plant.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Alcohol	(CAS-No.) 64-17-5 (EC-No.) 200-578-6 (EC Index-No.) 603-002-00-5 (REACH-no) 01-2119457610-43	60 – 70	Flam. Liq. 2, H225
ISOPROPYL ALCOHOL	(CAS-No.) 67-63-0 (EC-No.) 200-661-7 (EC Index-No.) 603-117-00-0 (REACH-no) 01-2119457558-25	1 – 10	Flam. Liq. 2, H225 Acute Tox. 4 (Oral), H302 Acute Tox. 4 (Dermal), H312 Eye Irrit. 2, H319 STOT SE 3, H336
Glycerides, C8-10 mono-, di-, and tri-, ethoxylated	(CAS-No.) 308067-11-0	1 – 10	Eye Irrit. 2, H319

Specific concentration limits:

Name	Product identifier	Specific concentration limits
Alcohol	(CAS-No.) 64-17-5 (EC-No.) 200-578-6 (EC Index-No.) 603-002-00-5 (REACH-no) 01-2119457610-43	(50 ≤C < 100) Eye Irrit. 2, H319

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general : Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).

First-aid measures after inhalation : Allow affected person to breathe fresh air. Allow the victim to rest.

First-aid measures after skin contact : None under normal use. Rinse skin with water/shower. Take off immediately all contaminated clothing.

First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

First-aid measures after ingestion : Get medical advice/attention if you feel unwell. Drink plenty of water. Do NOT induce vomiting. Rinse mouth. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects : Not applicable.

Foam Alcohol Hand Rub

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Symptoms/effects after eye contact : Causes serious eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Not applicable.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Carbon dioxide. Dry powder. Foam. Sand. Water spray.
Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

Fire hazard : Highly flammable liquid and vapour.
Explosion hazard : May form flammable/explosive vapour-air mixture.
Hazardous decomposition products in case of fire : Not applicable.

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.
Other information : Not applicable.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Take up liquid spill into absorbent material. Remove ignition sources. Use special care to avoid static electric charges. No open flames. No smoking.

6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.
Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Take up liquid spill into absorbent material. Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.
Other information : Can be slippery on hard, smooth walking area.

6.4. Reference to other sections

For further information refer to section 13. See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Additional hazards when processed : Handle empty containers with care because residual vapours are flammable.
Precautions for safe handling : Not applicable. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. No open flames. No smoking. Use only non-sparking tools.
Hygiene measures : None under normal use. Wash hands, forearms and face thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures : Comply with applicable regulations. Proper grounding procedures to avoid static electricity should be followed. Ground/bond container and receiving equipment. Use explosion-proof electrical/ventilating/lighting equipment.
Storage conditions : Keep only in original container. Keep cool. Keep only in the original container in a cool, well ventilated place away from : Keep in fireproof place. Keep container tightly closed.
Incompatible products : Strong bases. Strong acids.
Incompatible materials : Sources of ignition. Direct sunlight. Heat sources.

7.3. Specific end use(s)

Not applicable.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Foam Alcohol Hand Rub

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ISOPROPYL ALCOHOL (67-63-0)		
Ireland	Local name	Isopropyl alcohol
Ireland	OEL (8 hours ref) (ppm)	200 ppm
Ireland	OEL (15 min ref) (ppm)	400 ppm
Ireland	Notes (IE)	Sk (Substances which have the capacity to penetrate intact skin when they come in contact with it, and be absorbed into the body)
Ireland	Regulatory reference	Code of Practice for the Chemical Agents Regulations 2018
United Kingdom	Local name	Propan-2-ol
United Kingdom	WEL TWA (mg/m³)	999 mg/m³
United Kingdom	WEL TWA (ppm)	400 ppm
United Kingdom	WEL STEL (mg/m³)	1250 mg/m³
United Kingdom	WEL STEL [ppm]	500 ppm
United Kingdom	Regulatory reference	EH40/2005 (Third edition, 2018). HSE
Alcohol (64-17-5)		
Ireland	Local name	Ethanol
Ireland	OEL (15 min ref) (ppm)	1000 ppm
Ireland	Regulatory reference	Code of Practice for the Chemical Agents Regulations 2018
United Kingdom	Local name	Ethanol
United Kingdom	WEL TWA (mg/m³)	1920 mg/m³
United Kingdom	WEL TWA (ppm)	1000 ppm
United Kingdom	Regulatory reference	EH40/2005 (Third edition, 2018). HSE

<tx : _OFFICIAL_EIGA0759>

8.2. Exposure controls

Personal protective equipment:

Avoid all unnecessary exposure.

Hand protection:

Wear protective gloves.

Eye protection:

None under normal use. Chemical goggles or safety glasses

Respiratory protection:

None under normal use. Wear appropriate mask

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: Transparent.
Colour	: clear.
Odour	: odourless.
Odour threshold	: No data available
pH	: 5.5 – 6.5
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: > 78 °C
Flash point	: 22 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Highly flammable liquid and vapour.

Foam Alcohol Hand Rub

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 0.87 – 0.876
Solubility	: No data available
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: 10 – 12 seconds (DIN 53211)
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Not applicable.

10.2. Chemical stability

Not applicable. Highly flammable liquid and vapour. May form flammable/explosive vapour-air mixture.

10.3. Possibility of hazardous reactions

Not applicable. Not established.

10.4. Conditions to avoid

Not applicable. Direct sunlight. Extremely high or low temperatures. Open flame.

10.5. Incompatible materials

Not applicable. Strong acids. Strong bases.

10.6. Hazardous decomposition products

Not applicable. fume. Carbon monoxide. Carbon dioxide. May release flammable gases.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

ISOPROPYL ALCOHOL (67-63-0)	
LD50 oral rat	2000 mg/kg
LD50 oral	4396 mg/kg bodyweight
LD50 dermal rat	2000 mg/kg
LD50 dermal	12800 mg/kg bodyweight
LC50 Inhalation - Rat (Dust/Mist)	46600 mg/l

Alcohol (64-17-5)	
LD50 oral rat	7060 mg/kg
LD50 oral	10470 mg/kg bodyweight
LD50 dermal rabbit	> 16000 mg/kg
LD50 dermal	15800 mg/kg bodyweight
LC50 Inhalation - Rat	> 20 mg/l/4h
LC50 Inhalation - Rat (Dust/Mist)	> 99999 mg/l

Skin corrosion/irritation	: Not classified pH: 5.5 – 6.5
Additional information	: Based on available data, the classification criteria are not met
Serious eye damage/irritation	: Causes serious eye irritation. pH: 5.5 – 6.5
Respiratory or skin sensitisation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Germ cell mutagenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Carcinogenicity	: Not classified

Foam Alcohol Hand Rub

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Additional information	: Based on available data, the classification criteria are not met
Reproductive toxicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-single exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-repeated exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Aspiration hazard	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Potential adverse human health effects and symptoms	: Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Hazardous to the aquatic environment, short-term (acute)	: Not classified
Hazardous to the aquatic environment, long-term (chronic)	: Not classified

ISOPROPYL ALCOHOL (67-63-0)	
LC50 fish 1	100 mg/l
EC50 Daphnia 1	100 mg/l
EC50 other aquatic organisms 1	13299 mg/l waterflea
EC50 other aquatic organisms 2	> 1000 mg/l
Alcohol (64-17-5)	
LC50 fish 1	13000 mg/l
EC50 Daphnia 1	9300 mg/l
EC50 other aquatic organisms 1	5012 mg/l waterflea
EC50 other aquatic organisms 2	275 mg/l

12.2. Persistence and degradability

Foam Alcohol Hand Rub	
Persistence and degradability	Not applicable. Not established.
Alcohol (64-17-5)	
Persistence and degradability	Not established.

12.3. Bioaccumulative potential

Foam Alcohol Hand Rub	
Bioaccumulative potential	Not applicable. Not established.
ISOPROPYL ALCOHOL (67-63-0)	
Partition coefficient n-octanol/water (Log Pow)	0.05
Alcohol (64-17-5)	
Partition coefficient n-octanol/water (Log Pow)	-0.32
Bioaccumulative potential	Not established.

12.4. Mobility in soil

Foam Alcohol Hand Rub	
Ecology - soil	Not applicable.

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Other adverse effects	: Not applicable.
Additional information	: Avoid release to the environment.

Foam Alcohol Hand Rub

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Refer to manufacturer/supplier for information on recovery/recycling. Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

Additional information : Handle empty containers with care because residual vapours are flammable.

Ecology - waste materials : Avoid release to the environment.

SECTION 14: Transport information


In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
1170	1170	1170	1170	1170
14.2. UN proper shipping name				
ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION)	ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION)	Ethanol solution	ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION)	ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION)
Transport document description				
UN 1170 ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION), 3, II, (D/E)	UN 1170 ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION), 3, II	UN 1170 Ethanol solution, 3, II	UN 1170 ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION), 3, II	UN 1170 ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION), 3, II
14.3. Transport hazard class(es)				
3	3	3	3	3
				
14.4. Packing group				
II	II	II	II	II
14.5. Environmental hazards				
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No	Dangerous for the environment : No	Dangerous for the environment : No
No supplementary information available				

14.6. Special precautions for user

- Overland transport

Classification code (ADR) : F1
Special provisions (ADR) : 144, 601
Limited quantities (ADR) : 1I
Excepted quantities (ADR) : E2
Packing instructions (ADR) : P001, IBC02, R001
Mixed packing provisions (ADR) : MP19
Portable tank and bulk container instructions (ADR) : T4
Portable tank and bulk container special provisions (ADR) : TP1
Tank code (ADR) : LGBF
Vehicle for tank carriage : FL
Transport category (ADR) : 2
Special provisions for carriage - Operation (ADR) : S2, S20
Hazard identification number (Kemler No.) : 33
Orange plates :



Tunnel restriction code (ADR) : D/E

Foam Alcohol Hand Rub

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

EAC code : •2YE

- Transport by sea

Special provisions (IMDG) : 144
Limited quantities (IMDG) : 1 L
Excepted quantities (IMDG) : E2
Packing instructions (IMDG) : P001
IBC packing instructions (IMDG) : IBC02
Tank instructions (IMDG) : T4
Tank special provisions (IMDG) : TP1
EmS-No. (Fire) : F-E
EmS-No. (Spillage) : S-D
Stowage category (IMDG) : A
Properties and observations (IMDG) : Colourless, volatile liquids. Pure ETHANOL: flashpoint 13°C c.c. Explosive limits: 3.3% to 19% Miscible with water.

- Air transport

PCA Excepted quantities (IATA) : E2
PCA Limited quantities (IATA) : Y341
PCA limited quantity max net quantity (IATA) : 1L
PCA packing instructions (IATA) : 353
PCA max net quantity (IATA) : 5L
CAO packing instructions (IATA) : 364
CAO max net quantity (IATA) : 60L
Special provisions (IATA) : A3, A58, A180
ERG code (IATA) : 3L

- Inland waterway transport

Classification code (ADN) : F1
Special provisions (ADN) : 144, 601
Limited quantities (ADN) : 1 L
Excepted quantities (ADN) : E2
Carriage permitted (ADN) : T
Equipment required (ADN) : PP, EX, A
Ventilation (ADN) : VE01
Number of blue cones/lights (ADN) : 1

- Rail transport

Classification code (RID) : F1
Special provisions (RID) : 144, 601
Limited quantities (RID) : 1L
Excepted quantities (RID) : E2
Packing instructions (RID) : P001, IBC02, R001
Mixed packing provisions (RID) : MP19
Portable tank and bulk container instructions (RID) : T4
Portable tank and bulk container special provisions (RID) : TP1
Tank codes for RID tanks (RID) : LGBF
Transport category (RID) : 2
Colis express (express parcels) (RID) : CE7
Hazard identification number (RID) : 33

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions
Contains no substance on the REACH candidate list

Foam Alcohol Hand Rub

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Contains no REACH Annex XIV substances

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Indication of changes:

Section	Changed item	Change	Comments
	Revision date	Added	
1.1	Name	Modified	
2.2	Precautionary statements (CLP)	Modified	
3	Composition/information on ingredients	Modified	

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:

Acute Tox. 4 (Dermal)	Acute toxicity (dermal), Category 4
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 2	Flammable liquids, Category 2
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H225	Highly flammable liquid and vapour.
H302	Harmful if swallowed.
H312	Harmful in contact with skin.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

SDS EU ANNEX II NEWELL

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.