

PHOTORESIST STRIPPER PC 155 (600-019)

Part No: 600-019 - 1 litre
600-019-5 - 25 litres
1 litre concentrate make 5 litres

Description

A Photoresist Stripper concentrate to make 5 litres of working solution to strip photoresist from Fotoboard, FPC-16 and other alkaline processed resists

Preparation

Mix 1 litre concentrate with 4 litres of tap water

Usage

Use in a Mega temperature controlled PCB processing tank at 45 – 50°C. The Photoresist should strip from the copper in 2 – 3 minutes, depending on age of the solution and how much use it has had.

Health and Safety

Full Health and Safety details are on the rear of this instruction sheet. A report by an occupational hygienist concluded that under the test conditions, **NO LOCAL VENTILATION IS REQUIRED** using this etchant in Mega's PCB processing tanks. A copy of this report is available upon request.

Associated Products

A range of associated products for use with this etchant are featured in our free product catalogue. Please telephone us for your free copy



Mega Electronics Limited

Mega House, Grip Industrial Estate,
Linton, Cambridge, CB1 6NR. England.
Telephone: +44 (0) 1223 893900
Fax: +44 (0) 1223 893894
email: sales@megauk.com
Web: www.megauk.com

SECTION 1 PRODUCT IDENTIFICATION AND MANUFACTURE

NAME: PHOTORESIST STRIPPER

PART NO: 600-019

12-15061

MANUFACTURER'S/SUPPLIERS NAME, REGISTERED ADDRESS AND

EMERGENCY TEL NO

MEGA ELECTRONICS LTD

THE GRIP INDUSTRIAL ESTATE

LINTON

CAMBRIDGE CB1 6NR

TEL NO: +44 (0) 1223 893900

ORGANISATIONS NAME & ADDRESS AT WHICH MANUFACTURED

GRAMOS CHEMICALS INT. LTD

WILLIAMS STREET

WEST BROMWICH

WEST MIDLANDS

B70 0BE

SECTION 2 COMPOSITION/INFORMATION ON INGREDIENTS

COMPONENT	%BY WT	CAS & EEC Nos:	HAZARD	R PHRASE
MONOETHANOLAMINE	25	141-53-5 205-483-3	Xn	NOS- 20/21/22
BUTOXYETHANOL	65	111-76-2 203-905-0		36/37/38

SECTION 3 HAZARDS IDENTIFICATION

HARMFUL. HARMFUL BY INGESTION. IRRITATING TO EYES AND
RESPIRATORY SYSTEM. AVOID CONTACT WITH SKIN AND EYES

SECTION 4 FIRST AID MEASURES

INHALATION: REMOVE FROM EXPOSURE. REST AND KEEP WARM. IF
EXPOSURE HAS BEEN GREAT OBTAIN MEDICAL ATTENTION

SKIN CONTACT: WASH THOROUGHLY WITH AMPLE SOAP AND WATER.
REMOVE CONTAMINATED CLOTHING. UNLESS CONTACT HAS BEEN SLIGHT
OBTAIN MEDICAL ATTENTION

EYE CONTACT: IRRIGATE THOROUGHLY WITH WATER FOR AT LEAST 10
MINUTES. OBTAIN MEDICAL ADVICE.

INGESTION: WASH OUT MOUTH THOROUGHLY WITH WATER AND GIVE
PLENTY OF WATER TO DRINK. OBTAIN MEDICAL ATTENTION.

MEDICAL NOTES: NONE

SECTION 5 FIRE FIGHTING MEASURES

EXTINGUISHING MEDIA

FOAM, DRY POWDER.

COMBUSTION PRODUCTS: N/A

FIRE/EXPLOSION SCENARIOS: N/A

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE FIGHTERS: N/A

SECTION 6 ACCIDENTAL RELEASE MEASURES

PERSONAL PROTECTION

WEAR RESPIRATORY PROTECTION. PREVENT SKIN AND EYE CONTACT.

ENVIRONMENTAL PRECAUTIONS

AVOID ENTRY INTO DRAINAGE SYSTEM AND EARTH.

WORKPLACE PRECAUTIONS

DO NOT EAT, DRINK OR SMOKE

METHODS FOR CLEARING UP

ABSORB IN SAND OR OTHER INERT MATERIAL AND PUT INTO SUITABLE
CONTAINER FOR DISPOSAL.

SECTION 7 HANDLING AND STORAGE

HANDLING PRECAUTIONS

HARMFUL IF SWALLOWED, IN CONTACT WITH SKIN AND BY INHALATION.
ALWAYS WEAR SUITABLE PROTECTIVE CLOTHING. IF USED ACCORDING TO
INSTRUCTIONS NO LOCAL EXHAUST VENTILATION IS REQUIRED

STORAGE INCLUDING ANY SPECIAL REQUIREMENTS (TEMPERATURE,
VENTILATION, ETC) STORE IN A COOL DRY PLACE. DO NOT STORE WITH
ACIDS OR OXIDISING MATERIALS.

SECTION 8 EXPOSURE CONTROL/PERSONAL PROTECTION

ENGINEERING CONTROLS/VENTILATION

NO LOCAL EXHAUST VENTILATION REQUIRED IF USED ACCORDING TO
INSTRUCTIONS

RESPIRATORY PROTECTION

WEAR PROTECTIVE MASK

EYE PROTECTION: WEAR SAFETY GOGGLES

HAND PROTECTION

WEAR PROTECTIVE RUBBER/VINYL GLOVES

SKIN PROTECTION

ALWAYS OBSERVE ALL USUAL PRECAUTIONS WHEN HANDLING CHEMICALS.
DO NOT EAT, DRINK OR SMOKE WHEN HANDLING.

SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE: LIQUID

COLOUR: CLEAR

ODOUR: ETHEREAL

ACIDITY/ALKALINITY pH: 12

BOILING POINT: 100°C

MELTING POINT °C:

FLASH POINT (Open/Closed Cup) 75 (CLOSED CUP)

AUTOIGNITION TEMP °C

THERMAL DECOMPOSITION °C:OXIDISING PROPERTIES:

EXPLOSIVE PROPERTIES:

EXPLOSIVE LIMITS AT at 25°C (% VOL IN AIR)

LOWER: **UPPER**

RELATIVE DENSITY: SOLID CONTENT %:

SOLUBILITY IN WATER:

SOLUBILITY IN ORGANIC SOLVENTS

VOLATILE CONTENT

VAPOUR PRESSURE mmHg at 20°C

RELATIVE VAPOUR DENSITY (air = 1):

(of principle component and name): 17.5

EVAPORATION RATE

(n-butyl acetate = 1):

CONDUCTIVITY:

SECTION 10 STABILITY AND REACTIVITY PROPERTIES

CONDITIONS TO AVOID:

MATERIALS TO AVOID

AVOID CONTACT WITH STRONG OXIDANTS

HAZARDOUS DECOMPOSITION PRODUCTS: NONE KNOWN

HAZARDOUS POLYMERISATION - MAY/WILL/NOT occur - State condition to
avoid. WILL NOT OCCUR.

SECTION 11 TOXICOLOGICAL INFORMATION

EFFECT OF EYE CONTACT:

IRRITATION LEADING TO WATERING AND BLURRED VISION

EFFECT OF SKIN CONTACT:

LD50 2050mg/Kg. IRRITATION FOLLOWED BY DRYING OF THE SKIN.

EFFECT OF INHALATION

LC50 2.4mg/litre. IRRITATION OF THE MUCUOUS MEMBRANE AND DIZZINESS

EFFECT OF INGESTION

Any known data on sensitisation carcinogenicity, mutagenicity, teratogenicity, or
narcosis NO EVIDENCE.

SECTION 12 ECOLOGICAL INFORMATION

SECTION 13 DISPOSAL CONSIDERATIONS

THE PREPARATION SHOULD BE DISPOSED OF ACCORDING TO LOCAL
GOVERNMENT REGULATIONS VIA AUTHORISED WASTE DISPOSAL
AGENCIES.

SECTION 14 TRANSPORT INFORMATION

UN-Nr: 2491 IATA CLASS: 8 PACKING GRP: III IMDG-Nr: 8169

IMDG CLASS: 8

SECTION 15 REGULATORY INFORMATION

PRODUCT LABEL DETAILS - PER CHIP REGULATION 9

PRODUCT TRADE NAME/DESIGNATION: PHOTORESIST STRIPPER

CONTAINS: MONOETHANOLAMINE 25%
2-BUTOXYETHANOL 65

HAZARD SYMBOL: Xn

RISK PHRASE NOs & WORDS:

R20/21/22 HARMFUL BY INHALATION. HARMFUL IN CONTACT WITH SKIN.
HARMFUL IF SWALLOWED.

R36/37/38 IRRITATING TO EYES. IRRITATING TO RESPIRATORY SYSTEM.
IRRITATING TO SKIN

SAFETY PHRASE NOs & WORDS:

S24/25 AVOID CONTACT WITH SKIN. AVOID CONTACT WITH EYES.