

## **LOCTITE<sup>®</sup> EA 9455**

Known as Hysol 9455 June 2014

#### PRODUCT DESCRIPTION

LOCTITE<sup>®</sup> EA 9455 provides the following product characteristics:

Technology	Ероху		
Chemical Type (Resin)	Ероху		
Chemical Type (Hardener)	Mercaptan		
Appearance (Resin)	Colorless liquid <sup>LMS</sup>		
Appearance (Hardener)	Clear colorless liquid <sup>LMS</sup>		
Appearance (Mixture)	Ultra clear liquid		
Viscosity	Low		
Components	Two part - Resin & Hardener		
Mix Ratio, by volume - Resin : Hardener	1:1		
Mix Ratio, by weight - Resin : Hardener	100 : 105		
Cure	Room temperature cure after mixing		
Application	Bonding		
Strength	High		
Specific Benefit	<ul> <li>Toughness</li> <li>Excellent electrical insulator</li> <li>Low shrinkage properties</li> <li>Ultra clear adhesive bondline</li> <li>Good peel resistance</li> </ul>		
Key Substrates	Plastics, Metals , Glass, Wood, Ceramics and Rubbers		

LOCTITE® EA 9455 is a fast-curing, toughened, low viscosity, industrial grade epoxy adhesive. Ideal for bonding and potting of optical components like sensors and lenses.

#### TYPICAL PROPERTIES OF UNCURED MATERIAL

**Resin Properties** 

Specific Gravity @ 25 °C 1.09 to 1.15<sup>LMS</sup>

Flash Point - See SDS

Viscosity, Brookfield - RVT, 25 °C, mPa·s (cP):

Spindle 5, speed 50 rpm, 1,200 to 2,750<sup>LMS</sup>

**Hardener Properties** 

Specific Gravity @ 25 °C 1.09 to 1.15<sup>LMS</sup>

Flash Point - See SDS

Viscosity, Brookfield - RVT, 25 °C, mPa·s (cP): Spindle 4, speed 20 rpm, 1,500 to 4,500<sup>LMS</sup>

#### **Mixed Properties**

Pot Life @ 25 °C, minutes:

10 g mass 2 to 7<sup>LMS</sup>

### TYPICAL CURING PERFORMANCE


**Fixture Time** 

Fixture time is defined as the time to develop a shear strength of 0.1  $\ensuremath{\text{N/mm}^2}$  .

Fixture Time, @ 22 °C, minutes 15

#### Cure Speed vs. Time/Temperature

LOCTITE® EA 9455 develops high strength at room temperature within 3 to 6 hours. The assembled parts will be fixtured for light handling (0.1 N/mm²) after 15 minutes at room temperature. Elevated temperatures may be used to accelerate the cure. The graph below shows the shear strength developed with time on grit blasted steel lap shears at different temperatures and tested according to ISO 4587.



#### TYPICAL PROPERTIES OF CURED MATERIAL

4 mm thick samples cured for 7 days @ 22  $^{\circ}\text{C}$ 

**Physical Properties:** 

Coefficient of Thermal Expansion ISO 11359-1, K<sup>-1</sup>:

Temperature Range: -15 °C to 25 °C 38×10-6
Temperature Range: 45 °C to 200 °C 191×10-6



# 1.2 mm thick samples cured for 7 days @ 22 °C Physical Properties: Shore Hardness ISO 969 Durameter D

Shore Hardness, ISO 868, Durometer D		50
Elongation, ISO 527-3,%		80
Tensile Strength, ISO 527-3	N/mm² (psi)	1.3 (190)
Tensile Modulus , ISO 527-3	N/mm² (psi)	60 (8,700)

#### **Electrical Properties:**

Dielectric Breakdown Strength IEC 60243-1, kv/mm	15.6
Volume Resistivity, IEC 60093, Ω·cm	900×10 <sup>15</sup>
Surface Resistivity, IEC 60093, Ω	90×10 <sup>15</sup>
Distriction Constant / Discipation Factor IEO 000E0	

Dielectric Constant / Dissipation Factor, IEC 60250:

1 KHZ	8.5 / 0.27
1 MHz	4.6 / 0.12
10 MHz	3.0 / 0.09

### TYPICAL PERFORMANCE OF CURED MATERIAL Adhesive Properties

Cured for 7 days @ 22 °C

Lap Shear Strength, ISO 4587: Mild steel (grit blasted) N/mm<sup>2</sup> 14 (2,000)(psi) Aluminum (abraded) N/mm<sup>2</sup> 6 (1,700)(Silicon Carbide Paper, A166 grit, (psi) P400A grade) Aluminum (acid etched) N/mm<sup>2</sup> 13 (1,900)(psi) Aluminum (anodised) N/mm<sup>2</sup> (psi) (1,000)Stainless steel N/mm<sup>2</sup> (1,300)(psi) Polycarbonate N/mm<sup>2</sup> (psi) (290)Nylon N/mm<sup>2</sup> 0.3 (psi) (40)Softwood (Deal) N/mm<sup>2</sup> (440)(psi) Hardwood (Teak) N/mm<sup>2</sup> (580)(psi) Wood (Fir) N/mm<sup>2</sup> (psi) (440)ABS N/mm<sup>2</sup> (psi) (290)**PVC** N/mm<sup>2</sup> 2 (psi) (290)GRP (Polyester resin matrix) N/mm<sup>2</sup> (psi) (440)180° Peel Strength ISO 8510-2: Mild Steel (grit blasted) N/mm 1.8 (10.3)(lb/in) Tensile Strength , ISO 6922: Mild steel (grit blasted) to Soda 12 N/mm<sup>2</sup> glass (psi) (1,700)Impact Resistance, ISO 9653:

#### TYPICAL ENVIRONMENTAL RESISTANCE

kJ/m<sup>2</sup>

(ft-lbs/in<sup>2</sup>)

3.5


(1.7)

Cured for 7 days @ 22 °C Lap Shear Strength , ISO 4587: Mild steel (grit blasted)

Mild Steel Blocks (grit blasted)


#### **Hot Strength**

Tested at temperature



#### **Heat Aging**

Cured for 5 days @ 22 °C on mild steel (grit blasted) lapshears with no induced gap. Stored in air at temperatures indicated and tested at 22°C.



#### **Chemical/Solvent Resistance**

Cured for 5 days @ 22  $^{\circ}$ C on mild steel (grit blasted) lapshears with no induced gap, immersed in conditions indicated and tested @ 22  $^{\circ}$ C.

		% of initial strength		
Environment	°C	500 h	1000 h	
Motor oil (10W30)	87	120	180	
Unleaded gasoline	22	150	150	
Water/glycol 50/50	87	0	0	
Salt/Fog ASTM B-117	22	5	0	
98% RH	40	20	10	
Water	22	50	30	
Acetone	22	100	100	
Isopropanol	22	135	100	

Tensile Strength, ISO 6922, Cured for 7 days @ 22 °C, Mild steel pin (grit blasted) to Soda glass

		% of initial strength	
Environment	°C	500 h	1000 h
98% RH	40	10	0

#### **GENERAL INFORMATION**

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

Where aqueous washing systems are used to clean the surfaces before bonding, it is important to check for compatibility of the washing solution with the adhesive.

#### **Directions for use**

- For best performance surfaces for bonding should be clean, dry and free of grease. For high strength structural bonds, special surface treatments can increase the bond strength and durability.
- 2. To use, resin and hardener must be blended. Product can be applied directly from dual cartridges by dispensing through the mixer head supplied. Discard the first 3 to 5 cm of bead dispensed. Using bulk containers, mix thoroughly by weight or volume in the proportions specified in the Product Description Matrix. For hand mixing, weigh or measure out the desired amount of resin and hardener and mix thoroughly. Mix approximately 15 seconds after uniform color is obtained.
- 3. It is recommended that this product is not mixed and cured in bulk quantities of greater than 20 g as excessive heat build-up can occur. Mixing smaller quantities will minimize the heat build-up.
- Apply the adhesive as quickly as possible after mixing to one surface to be joined. For maximum bond strength apply adhesive evenly to both surfaces. Parts should be assembled immediately after mixed adhesive has been applied.
- For working life please see section 'Typical Properties of Uncured Material'. Higher temperatures and larger quantities will shorten this working time.
- Keep the assembled parts from moving during cure. The joint should be allowed to develop full strength before subjecting to any service loads.
- 7. Excess uncured adhesive can be wiped away with organic solvent (e.g. Acetone).
- After use and before adhesive hardens, mixing and application equipment should be cleaned with hot soapy water.

#### Loctite Material Specification LMS

LMS dated May 18, 2005. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.

#### Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

#### Conversions

 $(^{\circ}C \times 1.8) + 32 = ^{\circ}F$   $kV/mm \times 25.4 = V/mil$  mm / 25.4 = inches  $N \times 0.225 = lb$   $N/mm \times 5.71 = lb/in$   $N/mm^2 \times 145 = psi$   $MPa = N/mm^2$   $MPa \times 145 = psi$   $N \cdot m \times 8.851 = lb \cdot in$   $N \cdot m \times 0.738 = lb \cdot ft$   $N \cdot mm \times 0.142 = oz \cdot in$  $mPa \cdot s = cP$ 

#### Disclaimer

#### Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits. The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

#### Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. 

® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1.3