

■ 610 watt electronic hammer drill
SBE 610 Impuls

metabo[®]
work. don't play.



- Selectible impulse mode for exact screw-driving and comfortable drilling
- Variospeed (V) electronics for infinitely variable speed change
- Thumbwheel for preselection of speed
- Compact, lightweight machine in pot design for permanent use
- cast aluminium gear housing for optimum heat dissipation and stability
- User-friendly guidance of machine exhaust in all working situations
- Clockwise and anticlockwise rotation
- Impact-proof Metabo quick-action keyless chuck Futuro Plus for quick tool change
- Spindle with hexagon recess for screwdriver bits
- Ergonomic housing design for ideal handling
- Rubber-coated handle: vibration-reduced, comfortable and safe

Torque	5 Nm
Drilling capacity in	
- Concrete/ Steel/ Softwood	12 mm / 10 mm / 20 mm
No load speed	0 - 3.100 /min
Rated input power	610 W
Output power	360 W
Rated load speed	1.900 /min
Maximum impact rate	62.000 /min
Collar diameter	43 mm
Drilling spindle thread	1/2" - 20 UNF
Chuck capacity	1,5 - 13 mm
Drilling spindle with hexagon recess	1/4" (6,35 mm)
Weight (without mains cable)	1,7 kg

Scope of delivery

quick-action keyless chuck Futuro Plus,
side handle, drilling depth guide,
carry case

Bestell-Nr: 6.06102.50

EAN-Code: 4007430163646