



## V34 PRO Hearing Loop Driver

V34-UK / V34-EU /  
V34-AUS / V34-USJ

Our highly efficient and powerful V34 PRO is a constant current hearing loop driver with single output for perimeter loops. It is designed for large facilities and venues.

It has a Class-D amplifier output stage and an audio subsystem built around advanced digital systems including an ARM Cortex processor and dual DSPs. Combined with a powerful CPU to ensure peak performance, the V34 PRO provides self-monitoring and email alerts, remote setup over local area networks, guided hearing loop setup to make installation simple, and excellent speech and music reproduction.

### Features

- Inbuilt guided hearing loop setup utilising an integral test signal generator
- Intelligent self-monitoring system supplies status emails on changes to driver functions
- Dual-DSP controlled automatic gain control and high frequency compensation for metal loss
- Class-D amplifier output stage capable of delivering 12ARMS @ >34VRMS
- Highly-rated custom heat-sinks and active cooling
- Integrated universal switch mode power supplies provide ultra-efficient power utilisation (up to 90% efficient)
- Constant current output stage
- Adjustable audio time delay for large distance audio syncing
- Intuitive and sleek user interface on a full colour LCD
- Adjust both drive and loop output levels using an embedded LAN service, minimizing installation time
- Settings/profiles saved to a USB storage device
- Continuous self-testing
- Integrated protection circuits with temperature, voltage, short circuit and DC detection
- Full width 1U 19" rack mount

### Applications

Suitable for large facilities and venues such as:

- Theatres
- Concert halls
- Places of worship
- Sports arenas
- Conference facilities

### Voltage and Current

- >34 VRMS @ 12A RMS

### Standards

- EN 62368-1
- UL 62368-1
- EN 55032 EMC
- EN 55035 EMC



Talk to us now:  
+44 (0) 1732 223900 (UK & ROW)  
+1 616 392 3400 (US & Canada)  
[www.contacta.co.uk](http://www.contacta.co.uk)

## Physical Data

Dimensions	Height – 44mm (1.73") Width – 433mm (17.04") Depth – 301mm (11.85")
Construction	Mild Steel
Finish	Black Powder Coated



## Technical Data

Audio Inputs	2 X line/microphone inputs (switchable) XLR or Euroblock	Line (optimised for -10dBV to 0dBV)
		Microphone (12V phantom power via 680Ω optimised for levels above -45dBV)
Loop Outputs	Outputs Voltage	1 x 34Vrms (96.1V pk-pk)
	Output Current	1 x 12Arms @ 1KHz (33.94A) pk-pk >1200 seconds (20 minutes)
	Loop Connector	1 x NL4
Audio System	Frequency Response	100Hz to 5KHz
	Distortion	THD<1% (-40dB) full current both channels driven
	Automatic Gain Control	DSP controlled, peak detecting
	High Frequency Compensation	7 DSP controlled, optimised stages
	Audio Signal Delay	10ms to 40ms
Display	Backlit TFT 480 x 128 pixels (95mm x 25mm)	
Control	Single Rotary Push Control	
Mains Input	Voltage	100V-120V / 200V-240V AC (universal auto switching with PFC)
	Frequency	50Hz/60Hz
	Connection	IEC
Cooling	Custom heatsink with temperature-controlled fan	

## Driver Area Coverage

Area		
1:1	1:2	1:3
702.25m <sup>2</sup>	882.00m <sup>2</sup>	1200.00m <sup>2</sup>

All perimeter loop areas calculated under the following conditions: Area at maximum driver current without voltage clipping at 1.6KHz \* Loop designed to achieve 0dB in centre of the area \* calculated with 25mm x 0.1mm flat copper tape \* loop cable installed on floor \* listening plane 1.2m

## Rear Connections



Talk to us now: +44 (0) 1732 223900 (UK & ROW)  
+1 616 392 3400 (US & Canada)  
[www.contacta.co.uk](http://www.contacta.co.uk)