


EXTRAGAIN TELEVISION AERIALS

XG



SPECIFICATION

Product Range:	XG8A	XG9BK	XG16EW
Forward Gain	15dBi	14.9dBi	17.2dB
Front/Back Ratio	27dB	26dB	27dB
Acceptance Angle deg ±	13°	16°	13°
Windage N (at 130km/h)	91N	80N	117N
Length	1429mm	1485mm	2335mm
Frequency Range	470-606MHz	470-734MHz	470-862MHz

Grouped aerials optimise performance whilst the large 16 element aerial design provides maximum gain and performance. All come complete with a saddle clamp dipole for easy installation.



TERRESTRIAL AERIAL FOR WEAK SIGNAL AREAS LTE TUNED FREEVIEW COMPATIBLE PREVENTS GHOSTING SADDLE & CLAMP ADJUSTABLE TILT WEATHER RESISTANT F-TYPE CONNECTION QUICK INSTALL PASSIVE POWERED BOX CARTON

EXTRAGAIN TELEVISION AERIALS

XG



SPECIFICATION

Product Range:	XG5T	XG5K	XG10T	XG10K
Forward Gain	12.5dBi	12.5dBi	14.5dBi	14.5dBi
Front/Back Ratio	24dB	24dB	27dB	27dB
Acceptance Angle deg ±	23°	23°	15°	15°
Windage N (at 130km/h)	64N	64N	93N	93N
Length	764mm	764mm	1347mm	1347mm
Frequency Range	470-790MHz	470-694MHz	470-790MHz	470-694MHz

The XG design of high gain aerials remain a favourite with many when maximum signal reception and rejection are required. The XG5 & XG10 come complete with sealed F connector dipole, whilst the grouped models provide a minimum bandwidth.



TERRESTRIAL AERIAL FOR WEAK SIGNAL AREAS LTE TUNED FREEVIEW COMPATIBLE PREVENTS GHOSTING SADDLE & CLAMP ADJUSTABLE TILT WEATHER RESISTANT F-TYPE CONNECTION QUICK INSTALL PASSIVE POWERED BOX CARTON