

# LOCTITE<sup>®</sup> SF 7025

Known as LOCTITE<sup>®</sup> 7025  
June 2014

## PRODUCT DESCRIPTION

LOCTITE<sup>®</sup> SF 7025 provides the following product characteristics:

<b>Technology</b>	Cyanoacrylate Activator
<b>Chemical Type</b>	Sulfenamide (active ingredient)
<b>Solvent</b>	n-Heptane
<b>Active Ingredient Concentration, %</b>	0.02 to 0.04 <sup>LMS</sup>
<b>Appearance (uncured)</b>	Transparent, colorless liquid <sup>LMS</sup>
<b>Viscosity</b>	Very low
<b>Cure</b>	Not applicable
<b>Application</b>	CA adhesive cure accelerator

LOCTITE<sup>®</sup> SF 7025 is used where increased cure speed of LOCTITE<sup>®</sup> cyanoacrylate adhesives is required. It is especially recommended for irregular surfaces such as wood or stone where localized large gaps may exist. These gaps will contain larger volumes of adhesive which will cure slowly in the absence of activator. LOCTITE<sup>®</sup> SF 7025 is also recommended for porous substrates.

## TYPICAL PROPERTIES

Specific Gravity @ 25 °C	0.68
Viscosity @ 20 °C, mPa·s (cP)	0.4
Drying Time @ 20 °C, seconds	≤60
On Part Life, hours	24
Flash Point - See SDS	

## TYPICAL PERFORMANCE

Fixture time and cure speed achieved as a result of using LOCTITE<sup>®</sup> SF 7025 depend on the adhesive used and the substrate bonded.

Fixture Time, ISO 4587, seconds:

Steel (degreased) using LOCTITE <sup>®</sup> 416™, single side activation	≤45 <sup>LMS</sup>
---	--------------------

(Fixture time is defined as the time to develop a shear strength of 0.1 N/mm<sup>2</sup>)

## Handling precautions

Activator must be handled in a manner applicable to highly flammable materials and in compliance with relevant local regulations.

The solvent can affect certain plastics or coatings. It is recommended to check all surfaces for compatibility before use.

## GENERAL INFORMATION

**This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected with a sealant for chlorine or other strong oxidizing materials.**

**For safe handling information on this product, consult the Safety Data Sheet (SDS).**

**Under no circumstances should activator and adhesive be mixed directly as liquids. Use only in a well ventilated area.**

## Directions for use

### Surface Activation

1. Apply one coating of activator to one of the surfaces to be bonded, (the most porous substrate), by light spray, brush or dipping. Ensure total coverage of the bond area. Contaminated surfaces may need special cleaning or degreasing prior to activation to remove any dissolvable contamination.
2. Allow LOCTITE<sup>®</sup> SF 7025 to fully evaporate from parts prior to bonding to avoid solvent entrapment within the bond joint.
3. Apply the Loctite cyanoacrylate product to the non-activated surfaces.
4. Assemble parts immediately, assuring correct positioning of the parts.
5. Maintain light contact pressure to prevent movement until the bond has fixtured, (typically 10 seconds).

### Loctite Material Specification<sup>LMS</sup>

LMS dated July 08, 2004. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.

### Storage

This activator is classified as **HIGHLY FLAMMABLE** and must be stored in an appropriate manner in compliance with relevant regulations. Do not store near oxidising agents or combustible materials. The product is light sensitive and accordingly, translucent containers should be kept in a dark place when not in use. Store product in the unopened container in a dry location. Storage information may also be indicated on the product container labelling.

**Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties.** Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel cannot assume responsibility for product which has been contaminated or stored under conditions other than those

previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

registered in the U.S. Patent and Trademark Office.

### Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$   
 $\text{kV/mm} \times 25.4 = \text{V/mil}$   
 $\text{mm} / 25.4 = \text{inches}$   
 $\mu\text{m} / 25.4 = \text{mil}$   
 $\text{N} \times 0.225 = \text{lb}$   
 $\text{N/mm} \times 5.71 = \text{lb/in}$   
 $\text{N/mm}^2 \times 145 = \text{psi}$   
 $\text{MPa} \times 145 = \text{psi}$   
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$   
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$   
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$   
 $\text{mPa}\cdot\text{s} = \text{cP}$

### Reference 1.1

#### Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

#### **In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:**

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

#### **In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

#### **In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

#### Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark