


PRODUCT DATA SHEET

 Part Number : **G573**

Type	Size	Rating	Description
Incandescent	G11	12V 100mA	G-3½ Edison screw lamp

Dimensions(mm):



TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
12	85	93	100	4.0	5.0	6.0	5000

Notes:

- 1 C-2V filament shape.
- 2 Bead colour: White or Clear
- 3 Cap type E10/13, nickel plated brass
- 4 Cap marking CML 12V 100mA
- 5 RoHS and REACH SVHC compliant

Issue # 1 : 15Dec15