


Part Number: 00000209

Type	Size	Rating	Description
Incandescent	G19	12V 5W	Double Contact Bayonet Lamp



Dimensions in millimetres

TEST VOLTS	POWER (W)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
13.5	-	5	-	-	-	-	-

Notes:

- 1 **Base Type** BA15d Nickel plated brass
- 2 **Filament Shape** C-2R
- 3 **Lamp Marking** 12V 5W with E marking
- 4 **Environmental** RoHS & REACH SVHC compliant