# 5W DIY AC to DC Converter - PCB Mount

# multicomp PRO

5W, AC-DC converter





# Features

- RoHS Compliant
- Ultra-wide 85 305VAC and 70 430VDC input voltage range
- Accepts AC or DC input (dual-use of same terminal)
- Operating ambient temperature range -40°C to +85°C
- · Multi application, flexible layout
- · Compact size, high power density, green power
- · Controllable life and adjustable cost
- · No-load power consumption 0.1W
- Output short circuit, over-current protection
- Designed to meet IEC/EN61558, IEC/EN60335 standards
- · IEC/EN/UL62368 safety approval

### **Description**

MP-LS05-13BxxR3 series is one of highly efficient green power AC-DC Converter series. They feature wide input range accepting either AC or DC voltage, high efficiency, low power consumption and reinforced isolation. All models are particularly suitable for industrial control, electric power, instrumentation and smart home applications which have high requirement for dimension and don't have high requirement on EMC. For extremely harsh EMC environment, we recommend using the application circuit show in Design Reference of this datasheet.

Selection Guide				
Part Number	Output Power	Nominal Output Voltage and Current	Efficiency at 230V AC (%) Typ.	Capacitive Load (µF) Max.
MP-LS05-13B03R3	3.3W	3.3V/1000mA	69	2200
MP-LS05-13B05R3		5V/1000mA	76	1500
MP-LS05-13B09R3		9V/560mA	77	680
MP-LS05-13B12R3	5W	12V/420mA	79	470
MP-LS05-13B24R3		24V/210mA	81	100

Note: 1. The nominal output voltage refers to the voltage applied to the load terminal after adding external circuits.

2. If the product is used in a severe vibration application, it needs to be glued and fixed.

Input Specifications					
Item	Operating Conditions	Min.	Тур.	Max.	Unit
Innut Valtage Dange	AC input	85		305	V AC
Input Voltage Range	DC input	70	]	430	V DC
Input Frequency		47	] -	63	Hz
Input Current	115V AC	]	0.2		
Input Current	230V AC			0.1	^
Inrush Current	115V AC		20		A
Inrush Current	230V AC		40		
Recommended External Input Fuse		,	1A, slow-blow, required (The actual use needs to be selected according to the application environment)		
Hot Plug			Unava	ailable	



# 5W DIY AC to DC Converter - PCB Mount



Output Specifications					
Item	Operating Conditions	Min.	Тур.	Max.	Unit
Output Voltage Accuracy	10% - 100% load		±5	-	
Line Regulation	Rated load		±1.5	-	%
Load Regulation	0%-100% load		±3	-	
Ripple & Noise*	20MHz bandwidth (peak-to-peak value) 10% - 100% load		80	150	mV
Temperature Coefficient			±0.15		%/°C
Stand-by Power Consumption	230V AC		0.1	0.15	W
Short-circuit Protection		Hico	cup, continuo	ous, self-reco	overy
Over-current Protection		≥110%lo, self-recovery			
Minimum Load		10	-	-	%

Note: 1. \* The "parallel cable" method is used for ripple and noise test, please refer to AC-DC Converter Application Notes for specific information;

# **General Specifications**

Item		Operating Conditions	Min.	Тур.	Max.	Unit	
Isolation	Input-Output	Electric Strength Test for 1min, leakage current <5mA	3000	-	-	V AC	
Operating Te	mperature		-40	-	+85	°C	
Storage Tem	perature		7 -40	-	+105	C	
Storage Hum	nidity		-	-	95	%RH	
		-55°C to +85°C	1.67	-	-	%/°C	
Power Derat	ing	85V AC to 100V AC	1.33	-	-	70/ C	
		277V AC to 305V AC	0.72	-	-	%/V AC	
Safety Standard			IEC/EN/UL6	62368, IEC/E	EN60335,	IEC/EN61558	
Safety Certification			IEC/EN/UL6	62368			
Safety Class			CLASS II				
MTBF			MIL-HDBK-	217F@25°C	°C1000,0	00 h	

Mechanical Specifications				
Case Material		26.4mm × 14.73mm × 11mm		
Weight DIP package		5.2g (Typ.)		
Cooling Method		Free air convection		






<sup>2.</sup> The product is able to work with 0%-10% load and with stable output.


# **5W DIY AC to DC** Converter - PCB Mount multicomp PRO



Electron	Electromagnetic Compatibility (EMC)					
	OF.	CISPR32/EN55032	5032 CLASS A (Application circuit 1, 4)			
Emissions	CE	CISPR32/EN55032	CLASS B (Application circuit 2, 3)			
Emissions	RE	CISPR32/EN55032	CLASS A (Application circuit 1, 4)			
	KE	CISPR32/EN55032	CLASS B (Application circuit 2, 3)			
	ESD	IEC/EN61000-4-2	Contact ±6KV / Air ±8KV	perf. Criteria B		
	RS	IEC/EN61000-4-3	10V/m	perf. Criteria A		
	FFT	IEC/EN61000-4-4	±2KV (Application circuit 1, 2)	perf. Criteria B		
	EFT	IEC/EN61000-4-4	±4KV (Application circuit 3, 4)	perf. Criteria B		
Immunity	Curao	IEC/EN61000-4-5	line to line ±1KV (Application circuit 1, 2)	perf. Criteria B		
,	Surge	IEC/EN61000-4-5	line to line±2KV (Application circuit 3, 4)	pen. Chiena b		
	CS	IEC/EN61000-4-6	10Vr.m.s	perf. Criteria A		
	Voltage dip, short interruption and voltage variation	IEC/EN61000-4-11	0%, 70%	perf. Criteria B		


### **Product Characteristic Curve**






### Note:

- 1 With an AC input between 85 -100V AC/277- 305V AC and a DC input between 70 120V DC/390 430V DC, the output power must be derated as per temperature derating curves;
- 2 This product is suitable for applications using natural air cooling; for applications in closed environment please consult factory or one of our FAE.








# 5W DIY AC to DC Converter - PCB Mount

# multicomp PRO

# **Additional Circuits Design Reference**



LS series additional circuits design reference

Part Number	C1(required)	C2 (required)	L1 (required)	C3 (required)	C4	CY1 (required)	TVS
MP-LS05-13B03R3	10μF/450V	820µF/6.3V					SMBJ7A
MP-LS05-13B05R3	(-25°C to +85°C, 85-305VAC input;	(solid-state capacitor)		100µF/35V			SIVIDJIA
MP-LS05-13B09R3	-40°C to +85°C,	470µF/16V	4.7uH/60mΩ		0.1µF/	1.0nF/	SMBJ12A
MP-LS05-13B12R3	165-305VAC input)	(solid-state capacitor)	/2.2A		50V	400VAC	SMBJ20A
MP-LS05-13B24R3	22µF/450V (-40°C to +85°C, 85-305VAC input)	220uF/35V		47μF/35V			SMBJ30A

### Note:

- 1. C1 is used as filter capacitor with AC input (must be connected externally) and as EMC filter capacitor with DC input (must be connected), and it is recommended to use the capacitor with ripple current >200mA@100KHz. If C1 capacity is more than 22μF, can not connect current limiting resistor R1(R1 is EMS protective circuit device, see application circuit).
- 2. We recommend using an electrolytic capacitor with high frequency and low ESR rating for C3 (refer to manufacture's datasheet), electrolytic capacitor can be used for C2 when applied in normal and high temperature environments. Combined with C2, L1, they form a pi-type filter circuit. Choose a capacitor voltage rating with at least 20% margin, in other words not exceeding 80%. C4 is a ceramic capacitor, used for filtering high frequency noise.
- 3. A suppressor diode (TVS) is recommended to protect the application in case of converter failure and specification should be 1.2 times of the output voltage.


### **Environmental Application EMC Solution**

	LS series environmental application EMC solution selection table						
Recommended circuit	Application environmental	Typical industry	Input voltage range	Environment temperature	Emissions	Immunity	
1	Basic application	None		-40°C to +85°C	CLASS A	CLASS III	
2	Indoor civil environment	Smart home/Home appliances (2Y)		-25°C to	CLASS B	CLASS	
2	Indoor general environment	Intelligent building/Intelligent agriculture	85V AC to 305V AC	+55°C	CLASS B	III	
3	Indoor industrial environment	Manufacturing workshop	000770	-25°C to +55°C	CLASS B	CLASS IV	
4	Outdoor general environment	ITS/Video monitoring/Charging point/Communication/Security and protection		-40°C to +85°C	CLASS A	CLASS IV	



# **5W DIY AC to DC** Converter - PCB Mount multicomp PRO






## **Electromagnetic Compatibility Solution--Recommended Circuit**

1. Application circuit 1——Basic application

Application environmental	Ambient temperature range	Immunity CLASS	Emissions CLASS
Basic application	-40°C to +85°C	CLASS III	CLASS A

FUSE (required)	1A/300V, slow-blow	
R1 (required)	12Ω/3W	
LDM	4.7mH/Max: 15Ω/Min: 0.2A	

# 2. Application circuit 2——Indoor civil /Universal system recommended circuits for general environment



Recommended circuit 2

Application environmental	Ambient temperature range	Immunity CLASS	Emissions CLASS
Indoor civil /general	-25°C to +55°C	CLASS III	CLASS B

Component	Recommended value	
R1 (required)	12Ω/3W	
LDM	1.2mH/Max: 4.0Ω/Min: 0.2A	
FUSE (required)	1A/300V, slow-blow	


Note 1: In the home appliance application environment, the two Y capacitors of the primary and secondary need to be externally connected (CY1/CY2, value at 2.2nF/250VAC), which can meet the EN60335 certification.

Note 2: According to the certification requirements, the X capacitor needs to be connected in parallel with the bleeder resistance, the recommended resistance value is less than  $3.8M\Omega$ , and the actual need to be selected according to the certification standard.



# **5W DIY AC to DC** Converter - PCB Mount multicomp PRO

### 3. Application circuit 3——Universal system recommended circuits for indoor industrial environment




Recommended circuit 3

Application environmental	Ambient temperature range	Immunity CLASS	Emissions CLASS
Indoor industrial	-25°C to +55°C	CLASS IV	CLASS B

Component	Recommended value		
MOV	S14K350		
CX	0.1μF/310VAC		
LDM	1.2mH/Max: 4.0Ω/Min: 0.2A		
R1 (required)	12Ω/3W		
FUSE (required)	2A/300V, slow-blow		

Note: According to the certification requirements, the X capacitor needs to be connected in parallel with the bleeder resistance, the recommended resistance value is less than  $3.8M\Omega$ , and the actual need to be selected according to the certification standard.

## 4. Application circuit 4——Universal system recommended circuits for outdoor general environment



Recommended circuit 4

Application environmental	Ambient temperature range	Immunity CLASS	Emissions CLASS
Outdoor general environment	-40°C to +85°C	CLASS IV	CLASS A




# **5W DIY AC to DC** Converter - PCB Mount multicomp



Component	Recommended value	
MOV	S14K350	
LDM	4.7mH/Max: 15Ω/Min: 0.2A	
R1 (required)	12Ω/2W	
FUSE (required)	2A/300V, slow-blow	

# **Dimensions and Recommended Layout**

MP-LS05-13BxxR3 series dimensions



Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

