


Part Number : **28620L**

Type	Size	Rating	Description
Incandescent	T5	12V 1.28W	T-1½ Wedge Base lamp

Dimensions(mm):



TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
13.5	86	95	104	6.0	7.0	8.0	6200(B _{63.2})

Notes:

- 1 W2x4.6d in accordance with IEC 61-1, (BS EN 60061-1), sheet 7004-94-x.
- 2 C-2V filament shape
- 3 Bead colour: Clear
- 4 Lamp marking VCH 12/1.2L with a date code
- 5 RoHS and REACH SVHC compliant

Issue # 1 : 22 Jan 10