


PRODUCT DATA SHEET

Part Number: W1122

Type	Size	Rating	Description
Incandescent	T10	24V 2W	T-3¼ Miniature Edison Screw Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
28	72	80	88	6.0	7.8	9.5	7,500

Notes:

- 1 **Base Type** E10/13 Nickel plated brass
- 2 **Filament Shape** C-2F
- 3 **Bead colour** White or clear
- 4 **Lamp Marking** CML 24V 2W
- 5 **Environmental** RoHS & REACH SVHC compliant