# WSLF



Vishay Dale

## Power Metal Strip<sup>®</sup> Resistors, Low Value (Down to 0.0003 $\Omega$ ), Surface-Mount



## LINKS TO ADDITIONAL RESOURCES



## **FEATURES**

• Power Metal Strip<sup>®</sup> all-welded construction is ideal for all types of current sensing, voltage division, and pulse applications



RoHS

COMPLIANT

- Solid metal nickel-chrome, manganese-copper, or manganese-copper-tin alloy resistive element with low TCR (< 20 ppm/°C)
- HALOGEN FREE Proprietary processing technique produces GREEN extremely low resistance values, down to (5-2008) 0.0003 Ω
- Sulfur resistance by construction that is unaffected by high sulfur environments
- Very low inductance (< 2 nH)</li>
- Low thermal EMF (< 3 µV/°C)</li>
- AEC-Q200 qualified (1)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

#### Notes

- Follow link to "Overview of Automotive Grade Products" for more details: www.vishav.com/doc?49924
- <sup>(1)</sup> Flame retardance test may not be applicable to some resistor technologies

STANDARD ELECTRICAL SPECIFICATIONS								
GLOBAL MODEL	SIZE	POWER RATING P <sub>70 °C</sub> <sup>(1)</sup> W	POWER RATING P <sub>100</sub> ∘c <sup>(2)</sup> W	TOLERANCE %	RESISTANCE VALUE RANGE Ω	E RESISTANCE VALUES CURRENTLY AVAILABLE <sup>(3)</sup> (typic Ω g/1000 μ		
	2512	6.0	3.0	1.0, 5.0	0.3m to 0.5m	0.3m, 0.5m	258	
WSLF2512	2512	5.0	3.0	1.0, 5.0	1m to 2m	1m, 1.3m, 2m	212	
	2512	4.0	2.0	1.0, 5.0	3m	3m	267	
	2512	3.0	2.0	1.0, 5.0	4m	4m	267	

Notes

- Part marking: no part marking on these parts
- <sup>(1)</sup> See Fig. 1 Ambient Temperature Derating
- <sup>(2)</sup> See Fig. 2 Terminal Temperature Derating
- <sup>(3)</sup> Other values may be available, contact factory

### **GLOBAL PART NUMBER INFORMATION**

Global Part Numbering: WSLF25121L000FEA (WSLF2512, 0.001 Ω, ± 1 %) (visit www.vishay.net Vishay Dale parts numbering manual for all options) W S L F 2 5 2 1 L 0 0 Е 1 0 F Δ SPECIAL (2) RESISTANCE VALUE GLOBAL MODEL TOLERANCE CODE PACKAGING CODE (1) (5 digits) (8 digits) (1 digit) (2 digits) (2 digits) WSLF2512 EA = lead (Pb)-free, tape / reel  $L = m\Omega$ **F** = ± 1.0 % Reserved for future  $L5000 = 0.0005 \ \Omega$ **J** = ± 5.0 % specials **1L000** = 0.0010  $\Omega$ 

#### Notes

(1) Packaging code: EB (lead (Pb)-free) are non-standard packaging codes designating 1000 piece reels. These non-standard packaging codes are identical to our standard EA (lead (Pb)-free), except that they have a package quantity of 1000 pieces

Follow link for customization capabilities: www.vishay.com/doc?48163

Revision: 30-Jun-2020

For technical questions, contact: <u>ww2bresistors@vishay.com</u>

Document Number: 30193

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000

www.vishay.com

Vishay Dale


## **TECHNICAL SPECIFICATIONS**

TECHNICAL SPECIFICATIONS				
UNIT	WSLF RESISTOR CHARACTERISTICS			
	$\pm$ 200 for 0.3 m $\Omega$ and 0.5 m $\Omega$			
ppm/°C	$\pm$ 170 for 1.0 m $\Omega$ and 1.3 m $\Omega$			
	$\pm$ 70 for 2 m $\Omega,$ 3 m $\Omega,$ and 4 m $\Omega$			
ppm/°C	< 20			
°C	-65 to +170			
V	(P x R) <sup>1/2</sup>			
	UNIT			

#### Notes

- (1) Component TCR total TCR that includes the TCR effects of the resistor element and the copper terminal
- <sup>(2)</sup> Element TCR only applies to the alloy used for the resistor element
- (3) Maximum working voltage the WSL is not voltage sensitive, but is limited by power / energy dissipation and is also not ESD sensitive

#### **DIMENSIONS** in inches (millimeters)



## **CONSTRUCTION OUTLINE**



- (1) Resistive element: element material used is dependent on resistance value. Refer to Element Material in table)
- (2) Terminal: solid copper
- (3) Terminal / element weld

#### Notes

3D models available: <u>www.vishay.com/doc?30335</u>

Surface mount solder profile recommendations: <u>www.vishay.com/doc?31052</u>

MODEL		DIMEN	ISIONS	SOLDER PAD DIMENSIONS			
	L	w	н	т	а	b	I
WSLF2512	0.250 ± 0.006 (6.35 ± 0.15)	0.120 ± 0.008 (3.02 ± 0.2)	$\begin{array}{c} 0.0138 \pm 0.0012 \\ (0.35 \pm 0.03) \end{array}$	0.045 - 0.016 (1.14 - 0.4)	0.071 (1.80)	0.13 (3.40)	0.13 (3.40)

GLOBAL	RESISTANCE	THERMAL	THICKNESS in inc		
MODEL	VALUE (mΩ)	RESISTANCE (°C/W)	D <sub>1</sub>	D <sub>2</sub>	ELEMENT MATERIAL
WSLF2512	0.3	3.8	0.040 (1.02)	0.040 (1.02)	Mn-Cu-Sn
	0.5	6.7	0.033 (0.84)	0.033 (0.84)	Mn-Cu
	1.0	12.1	0.017 (0.43)	0.017 (0.43)	Mn-Cu
	1.3	14.6	0.013 (0.33)	0.013 (0.33)	Mn-Cu
	2.0	17.1	0.028 (0.71)	0.028 (0.71)	Ni-Cr
	3.0	18.2	0.019 (0.48)	0.019 (0.48)	Ni-Cr
	4.0	18.5	0.014 (0.36)	0.014 (0.36)	Ni-Cr

#### Note

(1) The full power rating of Power Metal Strip resistors are dependent upon the ability of the circuit board to dissipate the heat energy created in the resistance element. It is recommended to follow common design practices for power semiconductors that ensure the junction temperature is maintained with in thermal limits by using large pad surfaces, thermal vias, heavier copper weights, internal layers as well as other thermal spreading features. The thermal resistance values provided function in the same manner as junction to terminal temperature

Revision: 30-Jun-2020	2	Document Number: 30193
F	For technical questions, contact:	

## **WSLF**

Vishay Dale




## **DERATING- AMBIENT TEMPERATURE**


## 


Fig. 1 - P70 °C of Standard Electrical Specification Table

## **PULSE CAPABILITY**









### www.vishay.com/resistors/power-metal-strip-calculator

PERFORMANCE					
TEST	CONDITIONS OF TEST	TEST LIMITS			
Thermal shock	-55 °C to +150 °C, 2000 cycles, 15 min at each extreme	± 0.5 %			
Short time overload	5 x rated power for 5 s	± 0.5 %			
Low temperature storage	-65 °C for 24 h	± 0.1 %			
High temperature exposure	2000 h at +170 °C	± 1.0 %			
Bias humidity	+85 °C, 85 % RH, 10 % bias, 1000 h	± 0.5 %			
Mechanical shock	100 g's for 6 ms, 5 pulses	± 0.2 %			
Vibration	Frequency varied 10 Hz to 2000 Hz in 1 min, 3 directions, 12 h	± 0.2 %			
Load life	2000 h at +70 °C, 1.5 h "ON", 0.5 h "OFF"	± 1.0 %			
Resistance to solder heat	+260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	± 0.5 %			
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7a and 7b not required	± 0.1 %			

PACKAGING <sup>(1)</sup>						
MODEL	REEL					
MODEL	TAPE WIDTH	DIAMETER	PIECES/REEL	CODE		
WSLF2512	12 mm / embossed plastic	330 mm / 13"	4000	EA		

#### Notes

Embossed carrier tape per EIA-481

<sup>(1)</sup> Additional packaging details at <u>www.vishay.com/doc?20051</u>

Revision: 30-Jun-2020

Document Number: 30193



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.