



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 10

SDS No. : 164832  
V005.5

LOCTITE SI 5130 WH CR310ML M/L

Revision: 28.11.2018

printing date: 26.11.2020

Replaces version from: 20.02.2015

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE SI 5130 WH CR310ML M/L

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Silicone sealant

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.2. Label elements

##### Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.3. Other hazards

None if used properly.

Evolves acetic acid during cure.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

**SECTION 3: Composition/information on ingredients****3.2. Mixtures****General chemical description:**

Acetoxy curing silicone

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Contains no dangerous substances exceeding the limits of the EU-Regulation

**SECTION 4: First aid measures****4.1. Description of first aid measures****Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

**Skin contact:**

Rinse with running water and soap.

Obtain medical attention if irritation persists.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

**Ingestion:**

Do not induce vomiting.

Seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

**4.3. Indication of any immediate medical attention and special treatment needed**

See section: Description of first aid measures

**SECTION 5: Firefighting measures****5.1. Extinguishing media****Suitable extinguishing media:**

Carbon dioxide, foam, powder

Fine water spray

**Extinguishing media which must not be used for safety reasons:**

None known

**5.2. Special hazards arising from the substance or mixture**

carbon oxides.

Silica fume

Formaldehyde

**5.3. Advice for firefighters**

Wear self-contained breathing apparatus.

**Additional information:**

In case of fire, keep containers cool with water spray.

**SECTION 6: Accidental release measures**

**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid contact with skin and eyes.  
Ensure adequate ventilation.

**6.2. Environmental precautions**

Do not let product enter drains.

**6.3. Methods and material for containment and cleaning up**

Scrape up as much material as possible.  
Ensure adequate ventilation.  
Store in a partly filled, closed container until disposal.  
Dispose of contaminated material as waste according to Section 13.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Use only in well-ventilated areas.  
Vapours should be extracted to avoid inhalation.  
Ensure that workrooms are adequately ventilated.  
Avoid skin and eye contact.

Hygiene measures:

Good industrial hygiene practices should be observed.  
Do not eat, drink or smoke while working.  
Wash hands before work breaks and after finishing work.

**7.2. Conditions for safe storage, including any incompatibilities**

Store in a cool, well-ventilated place.  
Refer to Technical Data Sheet  
Never allow product to get in contact with water during storage

**7.3. Specific end use(s)**

Silicone sealant

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational Exposure Limits

Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, INHALABLE DUST]		6	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		EH40 WEL
Acetic acid 64-19-7 [ACETIC ACID]	10	25	Time Weighted Average (TWA):	Indicative	ECTLV
Acetic acid 64-19-7 [ACETIC ACID]	20	50	Short Term Exposure Limit (STEL):	Indicative	ECTLV

#### Occupational Exposure Limits

Valid for  
Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, TOTAL INHALABLE DUST]		6	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		IR_OEL
Acetic acid 64-19-7 [ACETIC ACID]	10	25	Time Weighted Average (TWA):	Indicative OELV	IR_OEL
Acetic acid 64-19-7 [ACETIC ACID]	15	37	Short Term Exposure Limit (STEL):	Indicative OELV	IR_OEL
Acetic acid 64-19-7 [ACETIC ACID]	10	25	Time Weighted Average (TWA):	Indicative	ECTLV
Acetic acid 64-19-7 [ACETIC ACID]	20	50	Short Term Exposure Limit (STEL):	Indicative	ECTLV

#### Biological Exposure Indices:

None

### 8.2. Exposure controls:

Engineering controls:  
Ensure good ventilation/extraction.

**Respiratory protection:**

This recommendation should be matched to local conditions.

Use only in well-ventilated areas.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

**Hand protection:**

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Wear protective glasses.

Protective eye equipment should conform to EN166.

**Skin protection:**

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

**Advices to personal protection equipment:**

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

## SECTION 9: Physical and chemical properties

**9.1. Information on basic physical and chemical properties**

Appearance	paste white
Odor	mild
Odour threshold	No data available / Not applicable
pH	Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	Not determined
Flash point	> 150 °C (> 302 °F)
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure (20 °C (68 °F))	< 0,13 mbar
Relative vapour density:	No data available / Not applicable
Density (20 °C (68 °F))	1,04 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Partially soluble
Solubility (qualitative) (Solvent: Acetone)	Soluble
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable

Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**9.2. Other information**

No data available / Not applicable

**SECTION 10: Stability and reactivity****10.1. Reactivity**

Polymerises in presence of water.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

Stable under normal conditions of storage and use.

**10.5. Incompatible materials**

See section reactivity.

**10.6. Hazardous decomposition products**

Evolves acetic acid during cure.

At higher temperatures (>150C) may release formaldehyde (traces).

**SECTION 11: Toxicological information****General toxicological information:**

Acetic acid is liberated slowly upon contact with moisture.

Inhalation of vapors in high concentration may cause irritation of respiratory system

Acetic acid released during polymerisation of acetoxy curing RTV silicones is irritating to the eyes

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

**11.1. Information on toxicological effects****Acute oral toxicity:**

No data available.

**Acute dermal toxicity:**

No data available.

**Acute inhalative toxicity:**

No data available.

**Skin corrosion/irritation:**

No data available.

**Serious eye damage/irritation:**

No data available.

**Respiratory or skin sensitization:**

No data available.

**Germ cell mutagenicity:**

No data available.

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

No data available.

**STOT-single exposure:**

No data available.

**STOT-repeated exposure::**

No data available.

**Aspiration hazard:**

No data available.

**SECTION 12: Ecological information****General ecological information:**

Cured Loctite products are typical polymers and do not pose any immediate environmental hazards.

In the cured state contribution of this product to Environmental Hazards is insignificant in comparison to articles in which it is used.

Precautions required with respect to Environmental Hazards of articles in which this product is used should be considered.

Do not empty into drains / surface water / ground water.

**12.1. Toxicity****Toxicity (Fish):**

No data available.

**Toxicity (Daphnia):**

No data available.

**Chronic toxicity to aquatic invertebrates**

No data available.

**Toxicity (Algae):**

No data available.

**Toxicity to microorganisms**

No data available.

**12.2. Persistence and degradability**

The product is not biodegradable.

No substance data available.

**12.3. Bioaccumulative potential**

No data available.

No substance data available.

**12.4. Mobility in soil**

Cured adhesives are immobile.

No substance data available.

**12.5. Results of PBT and vPvB assessment**

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

**12.6. Other adverse effects**

No data available.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**



**Product disposal:**

Dispose of in accordance with local and national regulations.

**Disposal of uncleaned packages:**

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

**Waste code**

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

**SECTION 14: Transport information****14.1. UN number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.2. UN proper shipping name**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.3. Transport hazard class(es)**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.4. Packing group**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.5. Environmental hazards**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.6. Special precautions for user**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**

not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3 %  
(2010/75/EC)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

---

**SECTION 16: Other information**

---

**Further information:**

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**