



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 9

LOCTITE SI 5926 INST. GASKET known as 5926 Inst Gasket  
12x40ml EN/DE

SDS No. : 165213  
V005.1

Revision: 16.11.2018  
printing date: 26.11.2020

Replaces version from: 16.03.2017

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE SI 5926 INST. GASKET known as 5926 Inst Gasket 12x40ml EN/DE

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:  
Silicone sealant

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd  
Wood Lane End  
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000  
Fax-no.: +44 1442 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.2. Label elements

##### Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.3. Other hazards

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

None if used properly.

Evolves acetic acid during cure.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

##### Declaration of the ingredients according to CLP (EC) No 1272/2008:

Contains no dangerous substances exceeding the limits of the EU-Regulation

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

##### Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

##### Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

##### Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

##### Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

#### 4.2. Most important symptoms and effects, both acute and delayed

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

#### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

##### Suitable extinguishing media:

Carbon dioxide, foam, powder

Fine water spray

##### Extinguishing media which must not be used for safety reasons:

None known

#### 5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO<sub>2</sub>) and nitrogen oxides (NO<sub>x</sub>) can be released.

#### 5.3. Advice for firefighters

Wear self-contained breathing apparatus.

##### Additional information:

In case of fire, keep containers cool with water spray.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes.

Ensure adequate ventilation.

#### 6.2. Environmental precautions

Do not let product enter drains.

**6.3. Methods and material for containment and cleaning up**

Scrape up as much material as possible.  
Ensure adequate ventilation.  
Store in a partly filled, closed container until disposal.  
Dispose of contaminated material as waste according to Section 13.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Vapours should be extracted to avoid inhalation.  
See advice in section 8  
Ensure that workrooms are adequately ventilated.  
Avoid skin and eye contact.

Hygiene measures:

Wash hands before work breaks and after finishing work.  
Do not eat, drink or smoke while working.  
Good industrial hygiene practices should be observed.

**7.2. Conditions for safe storage, including any incompatibilities**

Store in a cool, well-ventilated place.  
Refer to Technical Data Sheet  
Never allow product to get in contact with water during storage

**7.3. Specific end use(s)**

Silicone sealant

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational Exposure Limits**

Valid for  
Great Britain

None

**Occupational Exposure Limits**

Valid for  
Ireland

| Ingredient [Regulated substance]        | ppm | mg/m <sup>3</sup> | Value type                        | Short term exposure limit category / Remarks | Regulatory list |
|---|-----|-------------------|-----------------------------------|--|-----------------|
| Acetic acid<br>64-19-7<br>[ACETIC ACID] | 10  | 25                | Time Weighted Average (TWA):      | Indicative OELV                              | IR_OEL          |
| Acetic acid<br>64-19-7<br>[ACETIC ACID] | 15  | 37                | Short Term Exposure Limit (STEL): | Indicative OELV                              | IR_OEL          |
| Acetic acid<br>64-19-7<br>[ACETIC ACID] | 10  | 25                | Time Weighted Average (TWA):      | Indicative                                   | ECLTV           |
| Acetic acid<br>64-19-7<br>[ACETIC ACID] | 20  | 50                | Short Term Exposure Limit (STEL): | Indicative                                   | ECLTV           |

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

Engineering controls:  
Ensure good ventilation/extraction.

Respiratory protection:  
Ensure adequate ventilation.  
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area  
Filter type: A (EN 14387)  
This recommendation should be matched to local conditions.

Hand protection:  
Chemical-resistant protective gloves (EN 374).  
Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):  
nitrile rubber (NBR;  $\geq$  0.4 mm thickness)  
Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):  
nitrile rubber (NBR;  $\geq$  0.4 mm thickness)  
This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:  
Wear protective glasses.  
Protective eye equipment should conform to EN166.

Skin protection:  
Wear suitable protective clothing.  
Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

|                            |                                      |
|----------------------------|--------------------------------------|
| Appearance                 | paste<br>blue                        |
| Odor                       | Acetic acid                          |
| Odour threshold            | No data available / Not applicable   |
| pH                         | Not applicable                       |
| Melting point              | No data available / Not applicable   |
| Solidification temperature | No data available / Not applicable   |
| Initial boiling point      | Not determined                       |
| Flash point                | > 100 °C (> 212 °F); Supplier method |
| Evaporation rate           | No data available / Not applicable   |
| Flammability               | No data available / Not applicable   |
| Explosive limits           | No data available / Not applicable   |
| Vapour pressure            | Not determined                       |
| Relative vapour density:   | No data available / Not applicable   |
| Density                    | 1,02 g/cm <sup>3</sup>               |

|  |                                    |
|--|------------------------------------|
| ( )                                    |                                    |
| Bulk density                           | No data available / Not applicable |
| Solubility                             | No data available / Not applicable |
| Solubility (qualitative)               | Not available.                     |
| (Solvent: Water)                       |                                    |
| Solubility (qualitative)               | Partially soluble                  |
| (Solvent: Acetone)                     |                                    |
| Partition coefficient: n-octanol/water | No data available / Not applicable |
| Auto-ignition temperature              | No data available / Not applicable |
| Decomposition temperature              | No data available / Not applicable |
| Viscosity                              | No data available / Not applicable |
| Viscosity (kinematic)                  | No data available / Not applicable |
| Explosive properties                   | No data available / Not applicable |
| Oxidising properties                   | No data available / Not applicable |

## 9.2. Other information

No data available / Not applicable

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Strong oxidizing agents.  
Polymerises in presence of water.

### 10.2. Chemical stability

Stable under recommended storage conditions.

### 10.3. Possibility of hazardous reactions

See section reactivity

### 10.4. Conditions to avoid

No decomposition if used according to specifications.

### 10.5. Incompatible materials

See section reactivity.

### 10.6. Hazardous decomposition products

At higher temperatures (>150C) may release formaldehyde (traces).  
Evolves acetic acid during cure.

## SECTION 11: Toxicological information

### General toxicological information:

Acetic acid is liberated slowly upon contact with moisture.  
Acetic acid released during polymerisation of acetoxy curing RTV silicones is irritating to the eyes  
Prolonged or repeated contact may cause skin irritation.  
Prolonged or repeated contact may cause eye irritation.

### 11.1. Information on toxicological effects

#### Acute oral toxicity:

No data available.

#### Acute dermal toxicity:

No data available.

**Acute inhalative toxicity:**

No data available.

**Skin corrosion/irritation:**

No data available.

**Serious eye damage/irritation:**

No data available.

**Respiratory or skin sensitization:**

No data available.

**Germ cell mutagenicity:**

No data available.

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

No data available.

**STOT-single exposure:**

No data available.

**STOT-repeated exposure::**

No data available.

**Aspiration hazard:**

No data available.

## SECTION 12: Ecological information

### General ecological information:

Do not empty into drains / surface water / ground water.

### 12.1. Toxicity

#### Toxicity (Fish):

No data available.

#### Toxicity (Daphnia):

No data available.

#### Chronic toxicity to aquatic invertebrates

No data available.

#### Toxicity (Algae):

No data available.

#### Toxicity to microorganisms

No data available.

### 12.2. Persistence and degradability

The product is not biodegradable.

No substance data available.

### 12.3. Bioaccumulative potential

No data available.

No substance data available.

### 12.4. Mobility in soil

Cured adhesives are immobile.

No substance data available.

### 12.5. Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

### 12.6. Other adverse effects

No data available.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product disposal:**

Dispose of in accordance with local and national regulations.

Collection and delivery to recycling enterprise or other registered elimination institution.

**Disposal of uncleaned packages:**

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

**Waste code**

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

**SECTION 14: Transport information****14.1. UN number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.2. UN proper shipping name**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.3. Transport hazard class(es)**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.4. Packing group**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.5. Environmental hazards**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.6. Special precautions for user**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**

not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3 %  
(2010/75/EC)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.



---

## SECTION 16: Other information

### **Further information:**

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**